



Mallory Sonalert Products, Inc.

Part #: **CRP048MD2GN1W**

Sales Outline Drawing

Revision: **B**



Specifications:

| | | | | |
|------------------------|--|--|--|---|
| Sound Level Category: | Medium - Loud | Medium | Medium | Medium - Loud |
| Mode of Operation: | Continuous | Slow Pulse @ 1PPS | Slow Pulse @ | Fast Pulse @ 15PPS |
| Loudness @ 2 FT: | 80 to 90 dB(A) Typ. | 75 to 85 dB(A) Typ. | 75 to 85 dB(A) Typ. | 80 to 90 dB(A) Typ. |
| Pulse Rate (PPS): | N/A | 1 | 0.5 | See Graph |
| Frequency: | 3000 ± 100 Hz | 2800 ± 100 Hz | 1000 ± 100 Hz | 1500 ± 200 Hz |
| Connection: | RED & BLACK WIRES | RED & BLACK WIRES; YELLOW WIRE TO (-) | RED & BLACK WIRES; BLUE WIRE TO (-) | RED & BLACK, BLUE, YELLOW WIRES TO (-) |
| Voltage Rating: | 28 to 48 VDC | | | |
| Current Draw: | 40mA MAX | | | |
| Housing Material: | 6/6 Nylon, Color: Black | | | |
| Storage Temperature: | -40° to +85° C | | | |
| Operating Temperature: | -40° to +85° C | | | |
| Panel Mounting: | Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. | | | |
| Knurled Nut: | Used to attach part to panel. The max recommended torque is 10 in-lbs. | | | |
| Weight (Typical): | 2.1 oz (60g) | | | |
| | Approved with use of ACC03. | | | |
| cUL Recognition: | Supply voltage shall employ Transient Voltage Surge Suppression. | | | |
| Options: | Please contact factory. | | | |

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED THROUGH PANEL. IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.