

Rittal – The System.

Faster – better – everywhere.

► CM Compact System Enclosures – CM 5120.500

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CM Compact System Enclosures – CM 5120.500

created: 19.03.2018 build on www.rittal.com/us-en



Product description

Material:	Housing: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Carbon steel, 3.0 mm
Surface finish:	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Color:	RAL 7035
Protection category IP to IEC 60 529:	IP 55 with selection of the appropriate base plate or trim panel
Protection category NEMA:	NEMA 12 with selection of the appropriate base plate or trim panel
IK code:	IK08
Supply includes:	Housing with hinged door(s) 3-point locking system with double-bit insert Mounting plate Open base for individual cable entry
Base material:	Carbon steel

Product features

Dimensions:	Height: 1200 mm (47 ") Width: 1000 mm (39 ") Depth: 400 mm (16 ")
Mounting plate:	Height: 1155 mm (45 ")

Width: 940 mm (37 ")

Number of doors:	2
Packaging unit:	1 pc(s).
Weight/packaging unit:	86 kg (189.6 lb.)
EAN:	4028177479807
Customs tariff number:	94032080
ETIM 6.0:	EC000261
ETIM 5.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 7.0/7.1:	27180101
eCl@ss 6.0/6.1:	27180101
eCl@ss 5.1/5.1.4:	27180102
Product description (long):	CM Compact system enclosure, WHD: 1000x1200x400 mm, Sheet steel, with mounting plate, two-door, open base

Approvals

Approvals:	CSA Lloyds Register of Shipping RRR UL + C-UL
Certificates:	IK-Code
Declarations:	Declaration of conformity