

Product type designation

Product description

SCALANCE XB213-3

Preset for PROFINET mode!

SCALANCE XB213-3 MANAGEABLE LAYER 2 IE-SWITCH 13X
10/100 MBITS/S RJ45 PORTS 3X MM FO ST-PORT 1X CONSOLE
PORT DIAGNOSTICS-LED REDUNDANT POWER SUPPLY TEMP.-
RANGE 0 DGR C UP TO +60 DGR C; DIN RAIL MOUNTING
PROFINET IO-DEVICE ETHERNET/IP CERTIFICATE DEFAULT
PROFINET



Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s
---------------	-----------------------

Interfaces / for communication / integrated

Number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	13
Number of 100 Mbit/s ST(BFOC) ports	
<ul style="list-style-type: none"> for multimode 	3

Interfaces / others

Number of electrical connections	
<ul style="list-style-type: none"> for operator console 	1
<ul style="list-style-type: none"> for management purposes 	1
<ul style="list-style-type: none"> for power supply 	1
<ul style="list-style-type: none"> for redundant voltage supply 	1
Type of electrical connection	
<ul style="list-style-type: none"> for operator console 	RJ11 port
<ul style="list-style-type: none"> for management purposes 	RJ45 port

- for power supply

6-pole terminal block

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> • external 	24 V
<ul style="list-style-type: none"> • external 	19.2 ... 28.8 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.41 A

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation 	0 ... 60 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP20

Design, dimensions and weight

Design	compact
Width	120 mm
Height	117 mm
Depth	109 mm
Net weight	0.5 kg
Material / of the enclosure	Plastic
Mounting type	
<ul style="list-style-type: none"> • 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	No
<ul style="list-style-type: none"> • S7-300 rail mounting 	No
<ul style="list-style-type: none"> • S7-1500 rail mounting 	No

Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of $<\sim 0.3\sim$ s	50
Cascading in cases of star topology	any (depending only on signal propagation time)

Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> • CLI 	Yes
<ul style="list-style-type: none"> • web-based management 	Yes
<ul style="list-style-type: none"> • MIB support 	Yes
<ul style="list-style-type: none"> • TRAPs via email 	Yes
<ul style="list-style-type: none"> • Configuration with STEP 7 	Yes
<ul style="list-style-type: none"> • RMON 	Yes

<ul style="list-style-type: none"> • Port mirroring 	Yes
<ul style="list-style-type: none"> • multiport mirroring 	No
<ul style="list-style-type: none"> • CoS 	Yes
<ul style="list-style-type: none"> • with IRT / PROFINET IO switch 	No
<ul style="list-style-type: none"> • PROFINET IO diagnosis 	Yes
<ul style="list-style-type: none"> • switch-managed 	Yes
Telegram length / for Ethernet / maximum	1522 byte
Protocol / is supported	
<ul style="list-style-type: none"> • Telnet 	Yes
<ul style="list-style-type: none"> • HTTP 	Yes
<ul style="list-style-type: none"> • HTTPS 	Yes
<ul style="list-style-type: none"> • TFTP 	Yes
<ul style="list-style-type: none"> • FTP 	Yes
<ul style="list-style-type: none"> • BOOTP 	No
<ul style="list-style-type: none"> • DCP 	Yes
<ul style="list-style-type: none"> • LLDP 	Yes
<ul style="list-style-type: none"> • EtherNet/IP 	Yes
<ul style="list-style-type: none"> • IGMP (snooping/querier) 	Yes
Identification & maintenance function	
<ul style="list-style-type: none"> • I&M0 - device-specific information 	Yes
<ul style="list-style-type: none"> • I&M1 – higher-level designation/location designation 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • SNMP v1 	Yes
<ul style="list-style-type: none"> • SNMP v2 	Yes
<ul style="list-style-type: none"> • SNMP v3 	Yes
Product functions / Diagnosis	
Product function	
<ul style="list-style-type: none"> • Port diagnostics 	Yes
<ul style="list-style-type: none"> • Statistics Packet Size 	Yes
<ul style="list-style-type: none"> • Statistics packet type 	Yes
<ul style="list-style-type: none"> • Error statistics 	Yes
<ul style="list-style-type: none"> • SysLog 	Yes
<ul style="list-style-type: none"> • loopback diagnostics 	Yes
Product functions / VLAN	
Product function	
<ul style="list-style-type: none"> • VLAN - port based 	Yes
<ul style="list-style-type: none"> • VLAN - protocol-based 	No
<ul style="list-style-type: none"> • VLAN - IP-based 	No
<ul style="list-style-type: none"> • VLAN dynamic 	No

Product functions / DHCP

Product function	
<ul style="list-style-type: none"> • DHCP client 	Yes

Product functions / Redundancy

Product function	
<ul style="list-style-type: none"> • Ring redundancy 	Yes
<ul style="list-style-type: none"> • High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	No
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • redundancy procedure STP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> • redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	No
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • Passive listening 	Yes

Product functions / Security

Product function	
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • Broadcast/Multicast/Unicast Limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes

Product functions / Time

Product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T10

<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-7
<ul style="list-style-type: none"> • for hazardous zone / from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T10
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-8
Certificate of suitability / CE marking	Yes
Certificate of suitability	EN 61000-6-2, EN 61000-6-10
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • Railway application in accordance with EN 50155 	No
<ul style="list-style-type: none"> • Railway application in accordance with EN 50124-1 	No
<ul style="list-style-type: none"> • KC approval 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com

Security information

Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com. (V3.4)</p>
----------------------	---

last modified:

07/07/2016