



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

NOTES:

- "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- "/S1525" SPECIAL WIRING. PINS 1 AND 3 CROSS (PIN 1 OF THE RK IS CONNECTED TO PIN 3 OF THE RS, PIN 3 OF THE RK IS CONNECTED TO PIN 1 OF THE RS).

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	 High Technology Sensors and Automation Controls	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com
MATERIAL	SEE SPECIFICATIONS	DRFT CBM	DATE 02/10/99	DESCRIPTION
FINISH	SEE SPECIFICATIONS	APVD	SCALE 1=1.0	RK 4.4T-*--RS 4.4T/S1525
		UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO.
		CONTACT TURCK FOR MORE INFORMATION		REV G
G UPDATE NOTES PER ECO		TR 04/04/12 38530		DO NOT SCALE THIS DRAWING
REV	DESCRIPTION	BY	DATE	ECO NO.
FILE: 777000867				SHEET 1 OF 1