


SPECIFICATIONS						
SFECII ICATIONS						
CONTACT CARRIER MATERIAL	NYLON OR TPU					
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW					
CONTACT MATERIAL/PLATING	BRASS/GOLD					
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL					
RATED CURRENT [A]	2.0 A					
RATED VOLTAGE [V]	60 VAC/75 VDC					
OUTER CABLE JACKET MATERIAL/COLOR	PVC/BLACK					
CONDUCTOR INSULATION MATERIAL	PVC					
NUMBER OF CONDUCTORS [AWG]	6x24 AWG					
DRAIN/SHIELD	24 AWG DRAIN/ALUM-POLYESTER FOIL SHIELD					
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)					
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP68, IP69K					



CABLE LENGTH	TOLERANCE				
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER				
STRIP LENGTH	TOLERANCE				
0-7mm	±0.5mm				
8-29mm	±1.0mm				
30-49mm	±2.0mm				
50-69mm	±3.0mm				
70-100mm	±4.0mm				
OVER 100mm	±5.0mm				

KMY

11/02/11

DATE

NOTES:

REV DESCRIPTION

D UPDATE CABLE DIAMETER

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

	RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology	3000 CAMPUS [MINNEAPOLIS, MN 1-800-544-7 (763) 553-73 (763) 553-07 turck.com		55441 7769 300 708 fax
	MATERIAL		DRFT RWC	DATE 05/15/07	DESCRIPTION RKC 8.6T-*-F	DCC 9 ST	
	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0	KKC 0.01-"-1	KSC 0.01	
		DRAWING ARE FOR REFERENCE ONLY	UNIT OF ME	ASUREMENT	IDENTIFICATION NO.		REV
	FINISH	CONTACT TURCK	MILLIMETER [INCH]		DENTIFICATION NO.		
3492	6 SEE SPECIFICATIONS	FOR MORE INFORMATION					
ECO N	0.		DO NOT SCALE	THIS DRAWING	FILE: 777001342	SHEET	1 OF 1

SOURCE DRAWING - FOR REFERENCE ONLY