

### Product type designation

### SCALANCE XR524-8C

SCALANCE XR524-8C; MANAGED IE SWITCH; LAYER 3  
 AVAILABLE W. KEY-PLUG; POWER SUPPLY 230V AC; 24 X  
 10/100/1000 MBIT/S RJ45; 8 X 100/1000 MBIT/S SFP; CONTAINS 8  
 COMBO PORTS; 24 PORTS CAN BE USED IN TOTAL; FAULT-  
 SIGNAL CONTACT; SELECT/SET-BUTTON; PROFINET-IO  
 DEVICE; REDUNDANCY FUNCTIONS; OFFICE FEATURES  
 (RSTP, VLAN, IGMP,...); C-PLUG IN SCOPE OF SUPPLY



### Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
---------------	------------------------------------

### Interfaces / for communication / integrated

Number of electrical connections	24
• for network components or terminal equipment	
Number of 100 Mbit/s ST(BFOC) ports	0
• for multimode	
Number of electrical connections	8
• for SFP	
Number of combo ports / with RJ45 interface for optical plug-in transceiver	8

### Interfaces / for communication / pluggable / maximum

Number of electrical connections	8
• for SFP	

### Interfaces / others

Number of electrical connections	1
• for operator console	

<ul style="list-style-type: none"> <li>• for management purposes</li> </ul>	1
<ul style="list-style-type: none"> <li>• for signaling contact</li> </ul>	1
<ul style="list-style-type: none"> <li>• for power supply</li> </ul>	1
<ul style="list-style-type: none"> <li>• for redundant voltage supply</li> </ul>	1
Type of electrical connection	
<ul style="list-style-type: none"> <li>• for operator console</li> </ul>	RJ11 port
<ul style="list-style-type: none"> <li>• for management purposes</li> </ul>	RJ45 port
<ul style="list-style-type: none"> <li>• for signaling contact</li> </ul>	2-pole terminal block
<ul style="list-style-type: none"> <li>• for power supply</li> </ul>	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> <li>• C-PLUG/KEY-PLUG</li> </ul>	Yes
Product feature / hot-swappable interface modules	Yes

### Signal-Inputs/outputs

Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> <li>• at DC / Rated value</li> </ul>	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> <li>• at DC / maximum</li> </ul>	0.1 A

### Supply voltage, current consumption, power loss

Type of voltage supply / redundant power supply unit	No
Type of voltage / of the supply voltage	AC
Supply voltage	
<ul style="list-style-type: none"> <li>• at AC</li> </ul>	230 V
<ul style="list-style-type: none"> <li>• at AC / rated value</li> </ul>	90 ... 264 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	3.15 A / 250 V
Consumed current / maximum	0.6 A

### Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> <li>• during operation</li> </ul>	-25 ... +60 °C
<ul style="list-style-type: none"> <li>• during storage</li> </ul>	-40 ... +85 °C
<ul style="list-style-type: none"> <li>• during transport</li> </ul>	-40 ... +85 °C
Relative humidity	
<ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
Protection class IP	IP20

### Design, dimensions and weight

Design	19" rack
Number of modular height units / relating to 19-inch cabinet	1
Width	449 mm
Height	44 mm

Depth	305 mm
Net weight	4.2 kg
Mounting type	
• 19-inch installation	Yes
• 35 mm DIN rail mounting	No
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
Type of cable outlet	Cable outlet at front

### Product properties, functions, components / general

Cascading in cases of star topology	any (depending only on signal propagation time)
-------------------------------------	---

### Product functions / management, configuration

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• RMON	Yes
• Port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
Telegram length / for Ethernet / maximum	9216 byte
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• IGMP (snooping/querier)	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes
Protocol / is supported	

• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

### Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
• SysLog	Yes

### Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	Yes
• VLAN - IP-based	Yes
• VLAN dynamic	Yes
Number of VLANs / maximum	255
Number of VLANs - dynamic / maximum	255
Protocol / is supported / GVRP	Yes

### Product functions / DHCP

Product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

### Product functions / Routing

Service / Routing / Note	IP routing in combination with KEY-PLUG XR-500, IPv6 available soon
Product function	
• Static IP routing	Yes
• Static IP routing IPv6	No
• dynamic IP routing	Yes
• dynamic IP routing IPv6	No
Protocol / is supported	
• RIPv2	Yes
• RIPv6	No
• OSPFv2	Yes
• OSPFv3 for IPv6	No
• VRRP	Yes
• VRRP for IPv6	No

## Product functions / Redundancy

Product function	
<ul style="list-style-type: none"> <li>• Ring redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul style="list-style-type: none"> <li>• media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure STP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• redundancy procedure MSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Passive listening</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• LACP</li> </ul>	Yes

## Product functions / Security

Product function	
<ul style="list-style-type: none"> <li>• ACL - MAC-based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• ACL - port/MAC-based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 802.1x (radius)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Broadcast/Multicast/Unicast Limiter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• broadcast blocking</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• SSH</li> </ul>	Yes

## Product functions / Time

Product function	
<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes
Type of time synchronization	IEEE 1588 available soon

## Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	available soon
<ul style="list-style-type: none"> <li>• for emitted interference</li> </ul>	EN 61000-6-4 (Class A)
<ul style="list-style-type: none"> <li>• for interference immunity</li> </ul>	EN 61000-6-2
Certificate of suitability / CE marking	Yes

Certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
• E1 approval	No
• E1 approval	No
• KC approval	Yes

### Further Information / Internet Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
• to website: Industrial communication	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAx Download Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

### Security information

Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a>. (V3.4)</p>
----------------------	--

**last modified:** 07/10/2016