

Thermomagnetic device circuit breaker - TMC 81C 20A - 2907573

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermomagnetic device circuit breaker, Width: 17.6 mm, Mounting type: DIN rail, Color: gray



Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	150.0 g
Country of origin	China

Technical data

General

Mounting type	DIN rail
Color	gray

Electrical data

Operating voltage	240 V AC
	277 V AC
	60 V DC
Rated current I_N	20 A
Rated short-circuit switching capacity I_{cn}	10 kA (IC)

Dimensions

Height	116 mm
Width	17.6 mm
Depth	65.7 mm

Ambient conditions

Thermomagnetic device circuit breaker - TMC 81C 20A - 2907573

Technical data

Ambient conditions


Ambient temperature (operation)	-35 °C ... 70 °C
---------------------------------	------------------

Standards and Regulations


Standards/specifications	UL 489 IEC 60947-2
--------------------------	--------------------

Drawings

Diagram



Dimensional drawing



Classifications

eCl@ss

eCl@ss 8.0	27130806
eCl@ss 9.0	27130806

ETIM

ETIM 5.0	EC000942
----------	----------