

Thermomagnetic device circuit breaker - TMC 82D 10A - 2907659

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermomagnetic device circuit breaker, Width: 35.3 mm, Mounting type: DIN rail, Color: gray



Key Commercial Data

Packing unit	1 STK
Custom tariff number	85362000
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

General

Mounting type	DIN rail
Color	gray

Electrical data

Operating voltage	240 V AC
	480 V AC
	60 V DC
	120 V DC (in series)
Rated current I_N	10 A
Rated short-circuit switching capacity I_{cn}	10 kA (IC)

Dimensions

Height	116 mm
Width	35.3 mm
Depth	65.7 mm

Ambient conditions

Ambient temperature (operation)	-35 °C ... 70 °C
---------------------------------	------------------

Thermomagnetic device circuit breaker - TMC 82D 10A - 2907659


Technical data

Standards and Regulations


Standards/specifications	UL 489 IEC 60947-2
--------------------------	--------------------

Drawings

Diagram



Dimensional drawing



Classifications

eCl@ss

eCl@ss 8.0	27130806
eCl@ss 9.0	27130806

ETIM

ETIM 5.0	EC000942
----------	----------