

Shrink sleeve - WMS 4,8 (30X9)R YE - 0800409

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Shrink sleeve, Roll, yellow, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2: without print, perforated, mounting type: slide on, cable diameter range: 1.6 - 4.8 mm, lettering field size: 30 x 9 mm

Why buy this product

- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- The sleeves are pre-assembled for optimum use of material
- The sleeves remain flexible after shrinking
- The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- Up to four markers per sleeve are separated by perforations
- UL 224 (125°C, 600 V, all tubing)
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 626767
GTIN	4046356626767

Technical data

Dimensions

Length (b)	30 mm
Width (a)	9 mm
Cable diameter	1.6 mm ... 4.8 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	yellow
Base element material	polyolefine

Shrink sleeve - WMS 4,8 (30X9)R YE - 0800409

Technical data

General

Type	Shrink sleeve
Components	halogen-free
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Number of individual labels	500
Number of individual labels per row	2
Marking mounting type	slide on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Approvals

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	---	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	---	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>