

Product type designation

SCALANCE X307-2EEC

SCALANCE X307-2EEC, MANAGED IE SWITCH, COMPACT; 5 X 10/100MBIT/S RJ45; 2 X 10/100/1000MBIT/S RJ45; 2 X 100MBIT/S LC FO PORTS; 24 V DC REDUNDANT POWER SUPPLY; LED-DIAGNOSTICS, FAULT SIGNAL CONTACT WITH SELECT/SET-BUTTON; PROFINET-IO DEVICE, NETWORK-MANAGEMENT, INTEGRATED REDUNDANCY MANAGER, OFFICE FEATURES (RSTP, VLAN, IGMP,...); C-PLUG IN SCOPE OF SUPPLY



Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
---------------	------------------------------------

Interfaces / for communication / integrated

Number of electrical connections	7
<ul style="list-style-type: none"> • for network components or terminal equipment 	7
Number of 100 Mbit/s SC ports	0
<ul style="list-style-type: none"> • for multimode 	0
Number of 1000 Mbit/s LC ports	2
<ul style="list-style-type: none"> • for multimode • for single mode (LD) 	2

Interfaces / others

Number of electrical connections	2
<ul style="list-style-type: none"> • for signaling contact 	2
<ul style="list-style-type: none"> • for power supply 	2
<ul style="list-style-type: none"> • for redundant voltage supply 	2
Type of electrical connection	2-pole terminal block
<ul style="list-style-type: none"> • for signaling contact 	2-pole terminal block

<ul style="list-style-type: none"> • for power supply 	2 x 4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> • C-PLUG 	Yes

Signal-Inputs/outputs

Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> • at DC / Rated value 	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> • at DC / maximum 	0.1 A

Supply voltage, current consumption, power loss

Type of voltage supply / redundant power supply unit	Yes
Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> • external 	24 V
<ul style="list-style-type: none"> • external 	19.2 ... 57.6 V
Supply voltage / 2 / Rated value	
<ul style="list-style-type: none"> • Type of voltage / 2 / of the supply voltage 	DC
Supply voltage / at DC	24 V
<ul style="list-style-type: none"> • rated value 	19.2 ... 57.6 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	T 4 A / 125 V
Consumed current / maximum	0.75 A
Power loss [W]	
<ul style="list-style-type: none"> • at DC / at 24 V 	12 W

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation 	-40 ... +70 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +70 °C
<ul style="list-style-type: none"> • Note 	A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
Relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP30

Design, dimensions and weight

Design	compact
Width	216 mm
Height	143 mm
Depth	110 mm
Net weight	2.03 kg
Product feature / conformal coating	No

Mounting type	Wall mounting is possible only with an additional wall bracket; 19" mounting only with installation of two X-300EEC switches in pairs using a mounting plate
<ul style="list-style-type: none"> • 19-inch installation 	Yes
<ul style="list-style-type: none"> • 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	Yes
<ul style="list-style-type: none"> • S7-300 rail mounting 	Yes
<ul style="list-style-type: none"> • S7-1500 rail mounting 	No

Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	100
Cascading in cases of star topology	any (depending only on signal propagation time)

Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> • CLI 	Yes
<ul style="list-style-type: none"> • web-based management 	Yes
<ul style="list-style-type: none"> • MIB support 	Yes
<ul style="list-style-type: none"> • TRAPs via email 	Yes
<ul style="list-style-type: none"> • Configuration with STEP 7 	Yes
<ul style="list-style-type: none"> • RMON 	Yes
<ul style="list-style-type: none"> • Port mirroring 	Yes
<ul style="list-style-type: none"> • multiport mirroring 	Yes
<ul style="list-style-type: none"> • CoS 	Yes
<ul style="list-style-type: none"> • with IRT / PROFINET IO switch 	No
<ul style="list-style-type: none"> • PROFINET IO diagnosis 	Yes
<ul style="list-style-type: none"> • switch-managed 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • Telnet 	Yes
<ul style="list-style-type: none"> • HTTP 	Yes
<ul style="list-style-type: none"> • HTTPS 	Yes
<ul style="list-style-type: none"> • TFTP 	Yes
<ul style="list-style-type: none"> • FTP 	Yes
<ul style="list-style-type: none"> • BOOTP 	Yes
<ul style="list-style-type: none"> • GMRP 	Yes
<ul style="list-style-type: none"> • DCP 	Yes
<ul style="list-style-type: none"> • LLDP 	Yes
<ul style="list-style-type: none"> • IGMP (snooping/querier) 	Yes
Identification & maintenance function	
<ul style="list-style-type: none"> • I&M0 - device-specific information 	Yes
<ul style="list-style-type: none"> • I&M1 – higher-level designation/location designation 	Yes

Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes
• SysLog	Yes

Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
Number of VLANs / maximum	255
Number of VLANs - dynamic / maximum	255
Protocol / is supported / GVRP	Yes

Product functions / DHCP

Product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

Product functions / Redundancy

Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes

<ul style="list-style-type: none"> • redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • Passive listening 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • STP/RSTP 	Yes
<ul style="list-style-type: none"> • STP 	Yes
<ul style="list-style-type: none"> • RSTP 	Yes
<ul style="list-style-type: none"> • MSTP 	No
<ul style="list-style-type: none"> • RSTP big network support 	Yes
<ul style="list-style-type: none"> • LACP 	Yes

Product functions / Security

Product function	
<ul style="list-style-type: none"> • ACL - MAC-based 	Yes
<ul style="list-style-type: none"> • ACL - port/MAC-based 	Yes
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • Broadcast/Multicast/Unicast Limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes

Product functions / Time

Product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes
<ul style="list-style-type: none"> • IEEE 1588 profile default 	Yes

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 508
<ul style="list-style-type: none"> • for hazardous zone / from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, UL 1604 and 2279-15, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2:2005
Certificate of suitability / CE marking	Yes

Standard	
• for EMC	IEC 61850, IEEE 1613
Certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
• C-Tick	Yes
• Railway application in accordance with EN 50155	No
• Railway application in accordance with EN 50124-1	No
• IEC 61850-3	Yes
• IEEE 1613	Yes
• KC approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	Yes
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	No
• Royal Institution of Naval Architects (RINA)	No
MTBF / at 40 °C	20.9 y

Further Information / Internet Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

07/08/2016