SIEMENS

Data sheet

6GK5408-8GS00-2AM2

Product type designation



SCALANCE XM408-8C

SCALANCE XM408-8C; MANAGED MODULAR IE SWITCH; 8 X 10/100/1000 MBIT/S RJ45; 8 X 100/1000 MBIT/S SFP; CONTAINS 8 COMBO PORTS; 8 PORTS USABLE IN TOTAL; EXPANDABLE UP TO 24 PORTS ELECTRICAL OR OPTICAL; LAYER 3 WITH KEY PLUG AVAILABLE MOUNTING DIN-/S7-PROFILE-RAIL PROFINET-IO DEVICE; REDUNDANCY FUNCTIONS; OFFICE FEATURES (RSTP, VLAN, IGMP,...); C-PLUG IN SCOPE OF SUPPLY

Transmission rate		
Transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s	
Number of ports / maximum	24	
Interfaces / for communication / maximum configuration for modular devices		
Number of electrical ports / maximum	24	
Number of electrical ports / with PoE / maximum	16	
Number of optical ports / maximum	24	
Interfaces / for communication / integrated		
Number of electrical connections		
 for network components or terminal equipment 	8; RJ45 with securing collar	
Number of 10/100/1000 Mbit/s RJ45 ports /		
Integrated		
with securing collar	8	
Number of electrical connections		
• for SFP	8; 100 Mbit/s or 1000 Mbit/s SFP plug-in transceiver	
Number of combo ports / with RJ45 interface for	8; 100 Mbit/s or 1000 Mbit/s SFP plug-in transceiver	

2

optical plug-in transceiver

Number of connectable extender modules

Transmission rate

Interfaces / for communication / pluggable / maximu	um
Number of 10/100/1000 Mbit/s RJ45 ports	
with securing collar	16
with securing collar / with PoE	16
Number of 100 Mbit/s LC ports	
• for multimode	24
• for single mode (LD)	24
• for single mode (LH+)	24
• for single mode (ELH200)	24
Number of 1000 Mbit/s LC ports	
• for multimode	24
• for single mode (LD)	24
• for single mode (LH)	24
• for single mode (LH+)	24
• for single mode (ELH)	24
Number of electrical connections	
• for SFP	24; 100 Mbit/s or 1000 Mbit/s SFP plug-in transceiver
Interfaces / others	
Number of electrical connections	4
• for operator console	1
• for management purposes	1
for signaling contact	1
for power supply	1
• for redundant voltage supply	1
Type of electrical connection	
• for operator console	RJ11 port
for management purposes	RJ45 port
for signaling contact	2-pole terminal block
for power supply	4-pole terminal block
Number of extender expansion interfaces	2
design of the removable storage	
C-PLUG/KEY-PLUG	Yes
Product feature / hot-swappable interface modules	Yes
Signal-Inputs/outputs	
Operating voltage / of the signaling contacts	
• at DC / Rated value	24 V
Operating current / of the signaling contacts	
• at DC / maximum	0.1 A
Supply voltage current consumption power less	
Supply voltage, current consumption, power loss Type of voltage supply / redundant power supply unit	No
. The stratege cappit, tradition power cappit and	

Type of voltage / of the supply voltage	DC
Supply voltage	
• external	24 V
• external	19.2 28.8 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	F 15 A / 125 V
Consumed current / maximum	2 A
Power loss [W]	
• at DC / at 24 V	48 W
Supplied active power / of PSE / with PoE	
• per port / maximum	30 W
• total / maximum	360 W
Permitted ambient conditions	
Ambient temperature	
during operation	-40 +70 °C
during storage	-40 +85 °C
during transport	-40 +85 °C
Relative humidity	
 at 25 °C / without condensation / during 	95 %
operation / maximum	
Protection class IP	IP20
Design, dimensions and weight	
Design	SIMATIC S7-1500 device design
Design Width	140 mm
Design Width Height	140 mm 147 mm
Design Width Height Depth	140 mm 147 mm 125 mm
Design Width Height Depth Net weight	140 mm 147 mm
Design Width Height Depth Net weight Mounting type	140 mm 147 mm 125 mm 1.15 kg
Design Width Height Depth Net weight Mounting type • 19-inch installation	140 mm 147 mm 125 mm 1.15 kg
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting	140 mm 147 mm 125 mm 1.15 kg No Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting	140 mm 147 mm 125 mm 1.15 kg No Yes No
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting	140 mm 147 mm 125 mm 1.15 kg No Yes No
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • s7-300 rail mounting • S7-1500 rail mounting	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting • S7-1500 rail mounting Product properties, functions, components / general Cascading in cases of star topology	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • s7-300 rail mounting • S7-1500 rail mounting Product properties, functions, components / general Cascading in cases of star topology Product functions / management, configuration Product function	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes any (depending only on signal propagation time)
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • s7-300 rail mounting • S7-1500 rail mounting Product properties, functions, components / general Cascading in cases of star topology Product functions / management, configuration Product function • CLI	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes Yes Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • s7-300 rail mounting • S7-1500 rail mounting Product properties, functions, components / general Cascading in cases of star topology Product functions / management, configuration Product function	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes Yes Yes Yes Yes Yes
Design Width Height Depth Net weight Mounting type • 19-inch installation • 35 mm DIN rail mounting • wall mounting • s7-300 rail mounting • S7-1500 rail mounting Product properties, functions, components / general Cascading in cases of star topology Product functions / management, configuration Product function • CLI	140 mm 147 mm 125 mm 1.15 kg No Yes No Yes Yes Yes Yes Yes

Configuration with STEP 7	Yes
• RMON	Yes
Port mirroring	Yes
 multiport mirroring 	Yes
• CoS	Yes
 PROFINET IO diagnosis 	Yes
• switch-managed	Yes
Telegram length / for Ethernet / maximum	9216 byte
Protocol / is supported	
● Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• IGMP (snooping/querier)	Yes
Identification & maintenance function	
 I&M0 - device-specific information 	Yes
 I&M1 – higher-level designation/location designation 	Yes
Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
Product functions / Diagnosis	
Product function	
Port diagnostics	Yes
Statistics Packet Size	Yes
 Statistics packet type 	Yes
• Error statistics	Yes
• SysLog	Yes
Product functions / VLAN	
Product function	Yes
VLAN - port based	
VLAN - protocol-based	Yes
• VLAN - IP-based	Yes
VLAN dynamic	Yes
Number of VLANs / maximum	255

Number of VLANs - dynamic / maximum	255
Protocol / is supported / GVRP	Yes
Product functions / DHCP	
Product function	
DHCP client	Yes
DHCP Option 82	Yes
DHCP Option 66	Yes
DHCP Option 67	Yes
Product functions / Routing	
Service / Routing / Note	IP routing in combination with KEY-PLUG XM-400, IPv6 available soon
Product function	
Static IP routing	Yes
 Static IP routing IPv6 	No
• dynamic IP routing	Yes
dynamic IP routing IPv6	No
Protocol / is supported	
• RIPv2	Yes
RIPnG for IPv6	No
OSPFv2	Yes
OSPFv3 for IPv6	No
• VRRP	Yes
VRRP for IPv6	No
Product functions / Redundancy	
Product function	
Ring redundancy	Yes
 High Speed Redundancy Protocol (HRP) 	Yes
 high speed redundancy protocol (HRP) with redundancy manager 	Yes
 high speed redundancy protocol (HRP) with standby redundancy 	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
 media redundancy protocol (MRP) with redundancy manager 	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
Passive listening	Yes
Protocol / is supported	

• LACP	Yes
Product functions / Security	
Product function	
ACL - MAC-based	Yes
 ACL - port/MAC-based 	Yes
• IEEE 802.1x (radius)	Yes
 Broadcast/Multicast/Unicast Limiter 	Yes
 broadcast blocking 	Yes
Protocol / is supported	
• SSH	Yes
Product functions / Time	
Product function	
 SICLOCK support 	Yes
Protocol / is supported	
• NTP	Yes
• SNTP	Yes
Type of time synchronization	IEEE 1588 available soon
Standards, specifications, approvals	
Standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-0: 2009, EN60079-15: 2010, II 3 G Ex nA IIC T4 Gc, KEMA 07 ATEX 0145 X, IECEx DEK 14.0025X
• for safety / from CSA and UL	UL 508, UL 60950-1, CSA C22.2 Nr. 60950-1-03
• for hazardous zone / from CSA and UL	ISA 12.12.01-2012 (Hazardous Location), Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2
Certificate of suitability / CE marking	Yes
Certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
KC approval	Yes
Marine classification association	
 American Bureau of Shipping Europe Ltd. (ABS) 	No
Bureau Veritas (BV)	No
Det Norske Veritas (DNV)	Yes
Germanische Lloyd (GL)	No
Lloyds Register of Shipping (LRS)	Yes
Nippon Kaiji Kyokai (NK)	Yes
 Polski Rejestr Statkow (PRS) 	Yes

Yes Royal Institution of Naval Architects (RINA) 28 y

MTBF / at 40 °C

Further Information / Internet Links

Internet-Link

• to website: Selector SIMATIC NET **SELECTION TOOL**

• to website: Industrial communication

• to website: Industry Mall

• to website: Information and Download Center

• to website: Image database

• to website: CAx Download Manager

• to website: Industry Online Support

http://www.siemens.com/snst

http://www.siemens.com/simatic-net

https://mall.industry.siemens.com

http://www.siemens.com/industry/infocenter

http://automation.siemens.com/bilddb

http://www.siemens.com/cax

https://support.industry.siemens.com

Security information

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Thirdparty products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com. (V3.4)

last modified:

07/07/2016