

Shock protection - EMPPR (27X15) - 0829535

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Shock protection, Sheet, transparent, unlabeled, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm



Why buy this product

- High level of mechanical and chemical stability
- Suitable for permanent outdoor use
- Stuck or snapped onto labeled CARRIER ... to protect the labeling
- Extremely thick, yet flexible and transparent shock protection

Key Commercial Data

Packing unit	50 STK
Minimum order quantity	50 STK
GTIN	 4 046356 614931
GTIN	4046356614931

Technical data

Dimensions

Length (b)	15 mm
Width (a)	27 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in a cool and dry place is recommended.

General

Color	transparent
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC

Shock protection - EMPPR (27X15) - 0829535

Technical data

General

RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	300 µm
Marking mounting type	snapped into marker carrier

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>