

Toolbox - CRIMPFOX 4 IN 1 SET - 1200102

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Tool for processing ferrules according to DIN 46228-4, 0.5 mm² to 2.5 mm², equipped with pressure lock, cutting, stripping, twisting, and crimping unit, with three magazines including a strip each of ferrules from 0.5 mm² ... 2.5 mm², packaged in a robust plastic case

Why buy this product

- ✓ Integrated pressure lock ensures consistently high-quality crimping
- ✓ Up to 30% time savings since the process steps required for assembling conductors can be carried out using only one tool
- ✓ Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- ✓ Robust and durable due to use of resistant plastics and annealed metals
- ✓ Visualized process flows directly on the pliers simplify operation



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 042398
GTIN	4055626042398

Technical data

Dimensions

Length (b)	180 mm
Width (a)	31.5 mm
Height	100 mm
Stripping length	8 mm

General

Compression	Indent crimp
Type of contact	Ferrules
Min. AWG, flexible, multi-strand	14

Toolbox - CRIMPFOX 4 IN 1 SET - 1200102

Technical data

General

AWG max., flexible, multi-strand	20
Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²
AWG min	20
AWG max	14
Maximum stripping length	11 mm
Weight	600 g
Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	-------------------------------------------------------------------------------------	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>