

Product type designation

SCALANCE W734-1 RJ45

IWLAN CLIENT, SCALANCE W734-1 RJ45, FOR USE IN USA ONLY, 1 RADIO, 2 R-SMA ANT. CONNECT., IFEATURES ONLY WITH KEY-PLUG, IEEE 802.11A/B/G/H/N, 2.4/5GHZ, BRUTTO DATA RATE 300 MBIT/S, 2 X RJ45 (MAX. 100 MBIT/S), POE INTEGRATED 2-PORT-SWITCH, 2X24V DC, IP30, PLUG-IN SLOT PLEASE NOTE NATIONAL APPROVALS. (CERT ID: MSN-W1-RJ-E2) SCOPE OF SUPPLY: MANUALS ON CD ROM, GERMAN / ENGLISH, 1 X TERMINAL BLOCK



Transmission rate

Transfer rate	
<ul style="list-style-type: none"> with WLAN / maximum 	300 Mbit/s
<ul style="list-style-type: none"> for Industrial Ethernet 	10 Mbit/s, 100 Mbit/s, 10 Mbit/s, 100 Mbit/s

Interfaces

Number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	2
<ul style="list-style-type: none"> for power supply 	1
<ul style="list-style-type: none"> for redundant voltage supply 	1
Type of electrical connection	
<ul style="list-style-type: none"> for network components or terminal equipment 	RJ45 socket
<ul style="list-style-type: none"> for power supply 	4-pole screw terminal, PoE
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes
<ul style="list-style-type: none"> KEY-PLUG 	Yes

Interfaces / wireless

Number of radio cards / permanently installed	1
---	---

Transmission mode / for multiple input multiple output (MIMO)	2x2
Number of spatial streams	2
Number of electrical connections / for external antenna(s)	2
Type of electrical connection / for external antenna(s)	R-SMA (socket)
Product feature / external antenna can be mounted directly on device	Yes

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
Supply voltage / 1 <ul style="list-style-type: none"> • from terminal block 	19.2 V
Supply voltage / 2 <ul style="list-style-type: none"> • from terminal block 	28.8 V
Supply voltage <ul style="list-style-type: none"> • from Power-over-Ethernet acc. to IEEE802.3at for type 1 and IEEE802.3af 	48 V
Consumed current <ul style="list-style-type: none"> • at DC / at 24 V / typical • with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical 	0.25 A 0.125 A
Power loss [W] <ul style="list-style-type: none"> • at DC / at 24 V / typical • with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical 	6 W 6 W

Permitted ambient conditions

Ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport 	-20 ... +60 °C -40 ... +85 °C -40 ... +85 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W774-1 RJ45 or W734-1 RJ45 product must be installed in an enclosure. To comply with EN 50021, this enclosure must meet the requirements of at least IP 54 in compliance with EN 60529.
Protection class IP	IP30

Design, dimensions and weight

Width	26 mm
Height	156 mm
Depth	127 mm
Width / of the enclosure / without antenna	26 mm
Height / of the enclosure / without antenna	147 mm

Depth / of the enclosure / without antenna	127 mm
Net weight	0.52 kg
Mounting type	wall mounting only if flat mounted
<ul style="list-style-type: none"> • S7-300 rail mounting 	Yes
<ul style="list-style-type: none"> • S7-1500 rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	Yes

Wireless frequencies

Operating frequency	
<ul style="list-style-type: none"> • for WLAN in 2.4 GHz frequency band 	2.41 ... 2.48 GHz
<ul style="list-style-type: none"> • for WLAN in 5 GHz frequency band 	4.9 ... 5.8 GHz

Product properties, functions, components / general

Product function / Access Point Mode	No
Product function / Client Mode	Yes
Product function	
<ul style="list-style-type: none"> • Dual Client 	No
<ul style="list-style-type: none"> • iPCF client 	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
<ul style="list-style-type: none"> • iPCF-MC Access Point 	No
<ul style="list-style-type: none"> • iPCF-MC client 	Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
Number of iPCF-capable radio modules	1

Product functions / management, configuration

Number of manageable IP addresses / in client	8
Product function	
<ul style="list-style-type: none"> • CLI 	Yes
<ul style="list-style-type: none"> • web-based management 	Yes
<ul style="list-style-type: none"> • MIB support 	Yes
<ul style="list-style-type: none"> • TRAPs via email 	Yes
<ul style="list-style-type: none"> • Configuration with STEP 7 	Yes
<ul style="list-style-type: none"> • configuration with STEP 7 in the TIA Portal 	Yes
<ul style="list-style-type: none"> • forced roaming with IWLAN 	No
<ul style="list-style-type: none"> • WDS 	No
Protocol / is supported	
<ul style="list-style-type: none"> • Address Resolution Protocol (ARP) 	Yes
<ul style="list-style-type: none"> • ICMP 	Yes
<ul style="list-style-type: none"> • Telnet 	Yes
<ul style="list-style-type: none"> • HTTP 	Yes
<ul style="list-style-type: none"> • HTTPS 	Yes
<ul style="list-style-type: none"> • TFTP 	Yes
<ul style="list-style-type: none"> • DCP 	Yes
<ul style="list-style-type: none"> • LLDP 	No

Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Product functions / Diagnosis

Product function	
• PROFINET IO diagnosis	Yes
• Link Check	No
• connection monitoring IP-Alive	No
• localization via Aeroscout	No
• SysLog	Yes

Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

Product functions / VLAN

Product function	
• function VLAN with IWLAN	No

Product functions / DHCP

Product function	
• DHCP client	Yes
• in Client Mode / DHCP server via LAN	No

Product functions / Security

Product function	
• ACL - MAC-based	No
• Management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes

Protocol / is supported	
• SSH	Yes

Product functions / Time

Protocol / is supported	
• SNTP	Yes
• SIMATIC Time	Yes

Standards, specifications, approvals

Standard	
----------	--

<ul style="list-style-type: none"> • for FM • for hazardous zone • for safety / from CSA and UL • for hazardous zone / from CSA and UL 	<p>FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4</p> <p>EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X</p> <p>UL 60950-1 CSA C22.2 No. 60950-1</p> <p>ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, CL. 1, Div. 2, GP. A,B,C,D, T4 / CL. 1, Zone 2, GP IIC</p>
<p>Certificate of suitability</p> <ul style="list-style-type: none"> • EC declaration of conformity • CE marking • C-Tick • CCC • E1 approval • Railway application in accordance with EN 50155 • NEMA TS2 • IEC 61375 • IEC 61850-3 • NEMA4X • Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af • Power-over-Ethernet according to IEEE802.3at for type 2 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>Yes</p> <p>Yes</p>
<p>Standard for wireless communication</p> <ul style="list-style-type: none"> • IEEE 802.11a • IEEE 802.11b • IEEE 802.11e • IEEE 802.11g • IEEE 802.11h • IEEE 802.11i • IEEE 802.11n 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
<p>Wireless approval</p>	<p>You will find the current list of countries at: www.siemens.de/funkzulassungen</p>
<p>Marine classification association</p> <ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • Bureau Veritas (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) 	<p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p>

Accessories

Further Information / Internet Links

Internet-Link

- to website: TIA Selection Tool
- to the website: IWLAN
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool><http://www.siemens.com/iwlan><https://mall.industry.siemens.com><http://www.siemens.com/industry/infocenter><http://automation.siemens.com/bilddb><http://www.siemens.com/cax><https://support.industry.siemens.com>

Security information

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

07/08/2016