

### Product type designation

### SCALANCE W788-2 M12 EEC

IWLAN ACCESS POINT, SCALANCE W788-2 M12 EEC (USA), ONLY FOR USE INSIDE OF USA, 2 RADIOS, 6 N-CON. ANT.CONNECT., IEEE 802.11A/B/G/H/N, 2.4/5GHZ, GROSS 450 MBIT/S PER RADIO, 1 X M12 (MAX. 1 GBIT/S), POE, 24VDC, IP65 (-40-+70 DGR C), CONFORMAL COATING POE, WPA2/802.11I/E, EN50155 PLEASE NOTE NATIONAL APPROVALS! (CERT ID: RAPN-W2-M12-E3) Contains MPCIE-R1-ABGN-U3 SCOPE OF SUPPLY: MANUALS ON CD, GERMAN/ENGLISH



### Transmission rate

#### Transfer rate

- with WLAN / maximum
- for Industrial Ethernet

450 Mbit/s

10 Mbit/s, 100 Mbit/s, 1000 Mbit/s, 10 Mbit/s, 1000 Mbit/s

### Interfaces

#### Number of electrical connections

- for network components or terminal equipment
- for power supply
- for redundant voltage supply

1

1

1

#### Type of electrical connection

- for network components or terminal equipment
- for power supply

M12 interface (8-pole, X-coded), PoE

M12 interface (4-pole, A-coded)

#### design of the removable storage

- C-PLUG
- KEY-PLUG

Yes

Yes

### Interfaces / wireless

#### Number of radio cards / permanently installed

2

Transmission mode / for multiple input multiple output (MIMO)	3x3
Number of spatial streams	3
Number of electrical connections / for external antenna(s)	6
Type of electrical connection / for external antenna(s)	N-Connect (socket)
Product feature / external antenna can be mounted directly on device	Yes

#### Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
Supply voltage / 1 <ul style="list-style-type: none"> <li>from M12 Power Connector (A-coded) for redundant power supply</li> </ul>	19.2 V
Supply voltage / 2 <ul style="list-style-type: none"> <li>from M12 Power Connector (A-coded) for redundant power supply</li> </ul>	28.8 V
Supply voltage <ul style="list-style-type: none"> <li>from Power-over-Ethernet acc. to IEEE802.3at for type 1 and IEEE802.3af</li> <li>from Power-over-Ethernet acc. to IEEE802.3at for type 2</li> </ul>	48 V 50 V
Consumed current <ul style="list-style-type: none"> <li>at DC / at 24 V / typical</li> <li>with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical</li> <li>with Power-over-Ethernet according to IEEE802.3at for type 2 / typical</li> </ul>	0.63 A 0.22 A 0.3 A
Power loss [W] <ul style="list-style-type: none"> <li>at DC / at 24 V / typical</li> <li>with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical</li> <li>with Power-over-Ethernet according to IEEE802.3at for type 2 / typical</li> </ul>	15 W 10.7 W 15 W

#### Permitted ambient conditions

Ambient temperature <ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> <li>during transport</li> </ul>	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	100 %
Ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W788-x or W748-x product must be installed in an enclosure. To comply with EN 50021, this enclosure must meet the requirements of at least IP 54 in compliance with EN 60529.

Protection class IP	IP65
---------------------	------

### Design, dimensions and weight

Width / of the enclosure / without antenna	200 mm
Height / of the enclosure / without antenna	176 mm
Depth / of the enclosure / without antenna	79 mm
Net weight	1.7 kg
Product feature / conformal coating	Yes
Mounting type	For mounting on 35 mm DIN rail, an additional mounting adapter is required
<ul style="list-style-type: none"> <li>• S7-300 rail mounting</li> <li>• S7-1500 rail mounting</li> <li>• wall mounting</li> </ul>	Yes Yes Yes

### Wireless frequencies

Operating frequency	
<ul style="list-style-type: none"> <li>• for WLAN in 2.4 GHz frequency band</li> <li>• for WLAN in 5 GHz frequency band</li> </ul>	2.41 ... 2.48 GHz 4.9 ... 5.8 GHz

### Product properties, functions, components / general

Product function / Access Point Mode	Yes
Product function / Client Mode	Yes
Number of SSIDs	16
Product function	
<ul style="list-style-type: none"> <li>• Dual Client</li> <li>• iPCF Access Point</li> <li>• iPCF client</li> <li>• iPCF-MC Access Point</li> <li>• iPCF-MC client</li> </ul>	No Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures' Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
Number of iPCF-capable radio modules	0
Product function / iREF	No; In combination only with 'KEY-PLUG W780 iFeatures'
Number of iREF-capable radio modules	0

### Product functions / management, configuration

Number of manageable IP addresses / in client	8
Product function	
<ul style="list-style-type: none"> <li>• CLI</li> <li>• web-based management</li> <li>• MIB support</li> <li>• TRAPs via email</li> <li>• Configuration with STEP 7</li> <li>• configuration with STEP 7 in the TIA Portal</li> <li>• operation with IWLAN controller</li> </ul>	Yes Yes Yes Yes Yes Yes No

<ul style="list-style-type: none"> <li>• operation with Enterasys WLAN controller</li> </ul>	No
<ul style="list-style-type: none"> <li>• forced roaming with IWLAN</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• WDS</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• Address Resolution Protocol (ARP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• ICMP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Telnet</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• HTTPS</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• TFTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• DCP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• LLDP</li> </ul>	Yes
Identification & maintenance function	
<ul style="list-style-type: none"> <li>• I&amp;M0 - device-specific information</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• I&amp;M1 – higher-level designation/location designation</li> </ul>	Yes

### Product functions / Diagnosis

Product function	
<ul style="list-style-type: none"> <li>• PROFINET IO diagnosis</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Link Check</li> </ul>	No
<ul style="list-style-type: none"> <li>• connection monitoring IP-Alive</li> </ul>	No
<ul style="list-style-type: none"> <li>• SysLog</li> </ul>	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• SNMP v1</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v2</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• SNMP v3</li> </ul>	Yes

### Product functions / VLAN

Product function	
<ul style="list-style-type: none"> <li>• function VLAN with IWLAN</li> </ul>	Yes

### Product functions / DHCP

Product function	
<ul style="list-style-type: none"> <li>• DHCP client</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• in Client Mode / DHCP server via LAN</li> </ul>	No

### Product functions / Redundancy

Protocol / is supported	
<ul style="list-style-type: none"> <li>• STP/RSTP</li> </ul>	Yes

### Product functions / Security

Product function	
<ul style="list-style-type: none"> <li>• Management security, ACL-IP based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 802.1x (radius)</li> </ul>	Yes

• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
Protocol / is supported	
• SSH	Yes

### Product functions / Time

Protocol / is supported	
• SNTP	Yes
• SIMATIC Time	Yes

### Standards, specifications, approvals

Standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for safety / from CSA and UL	UL 60950-1 CSA C22.2 No. 60950-1
• for hazardous zone / from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, CL. 1, Div. 2, GP. A,B,C,D, T4 / CL. 1, Zone 2, GP IIC
Certificate of suitability	
• EC declaration of conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• CCC	No
• E1 approval	Yes
• Railway application in accordance with EN 50155	Yes
• Railway application in accordance with EN 50121-4	Yes
• Fire protection in accordance with EN 45545-2	Yes
• NEMA TS2	Yes
• IEC 61375	No
• IEC 61850-3	No
• NEMA4X	No
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	Yes
• Power-over-Ethernet according to IEEE802.3at for type 2	Yes
Standard for wireless communication	
• IEEE 802.11a	Yes
• IEEE 802.11b	Yes
• IEEE 802.11e	Yes

<ul style="list-style-type: none"> <li>• IEEE 802.11g</li> <li>• IEEE 802.11h</li> <li>• IEEE 802.11i</li> <li>• IEEE 802.11n</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
Wireless approval	For operation in the USA, you can find more detailed information at: <a href="http://www.siemens.com/simatic-net/ik-info">www.siemens.com/simatic-net/ik-info</a>
Marine classification association	
<ul style="list-style-type: none"> <li>• American Bureau of Shipping Europe Ltd. (ABS)</li> <li>• Bureau Veritas (BV)</li> <li>• Det Norske Veritas (DNV)</li> <li>• Germanische Lloyd (GL)</li> <li>• Lloyds Register of Shipping (LRS)</li> <li>• Nippon Kaiji Kyokai (NK)</li> <li>• Polski Rejestr Statkow (PRS)</li> </ul>	<p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p>

### Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> <li>• to website: TIA Selection Tool</li> <li>• to the website: IWLAN</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAx Download Manager</li> <li>• to website: Industry Online Support</li> </ul>	<p><a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a></p> <p><a href="http://www.siemens.com/iwlan">http://www.siemens.com/iwlan</a></p> <p><a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a></p> <p><a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a></p> <p><a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a></p> <p><a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a></p> <p><a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a></p>

### Security information

Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <a href="http://www.siemens.com/industrialsecurity">http://www.siemens.com/industrialsecurity</a>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <a href="http://support.automation.siemens.com">http://support.automation.siemens.com</a>. (V3.4)</p>
----------------------	---

**last modified:** 07/08/2016