

## Cable - CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled shielded round cable; connection 1: D-SUB socket strip (1x 9-position); connection 2: D-SUB pin strip (1x 9-position); cable length: 6 m



### Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4017918893002

### Technical data

#### General

Nominal voltage $U_N$	25 V AC
	60 V DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Length of cable	6 m
Single wire, cross section	0.25 mm <sup>2</sup>
Single wire, cross section [AWG]	24
External diameter	7.5 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

#### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1

#### Connector 1

# Cable - CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049

## Technical data

### Connector 1

Connection name	Field level
Connection method	D-SUB pin strip
Number of connections	1
Number of positions	9

### Connector 2

Connection name	Controller level
Connection method	D-SUB socket strip
Number of connections	1
Number of positions	9

### Supported controller

Controller	universal
------------	-----------

### Color code

Connector 1 = connector 2 (optional) = wire color	D-SUB 9 (1) = D-SUB9 (1) = white
	D-SUB 9 (2) = D-SUB9 (2) = brown
	D-SUB 9 (3) = D-SUB9 (3) = green
	D-SUB 9 (4) = D-SUB9 (4) = yellow
	D-SUB 9 (5) = D-SUB9 (5) = gray
	D-SUB 9 (6) = D-SUB9 (6) = pink
	D-SUB 9 (7) = D-SUB9 (7) = blue
	D-SUB 9 (8) = D-SUB9 (8) = red
	D-SUB 9 (9) = D-SUB9 (9) = black

### Standards and Regulations

Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1
Connection in acc. with standard	CUL

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

#### Approvals


UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized


# Cable - CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049


## Approvals

Ex Approvals


### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		2 A	

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		2 A	

CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	70002966
Nominal voltage UN		125 V	
Nominal current IN		1 A	

EAC		RU C- DE.A*30.B00767	
-----	---	-------------------------	--

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
------------------	---	---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
 Flachsmarktstr. 8  
 32825 Blomberg  
 Germany  
 Tel. +49 5235 300  
 Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>