







Features

- Constant Voltage + Constant Current mode output
- Metal housing with class I design
- · Built-in active PFC function
- IP67 / IP65 rating for indoor or outdoor installations
- Function options: output adjustable via potentiometer;
 3 in 1 dimming
- Typical lifetime > 62000 hours
- 7 years warranty


Applications

- · LED street lighting
- · LED high-bay lighting
- Parking space lighting
- · LED fishing lamp
- LED greenhouse lighting
- Type "HL" for use in Class I, Division 2 hazardous (Classified) location.

Description

HLG-320H series is a 320W AC/DC LED driver featuring the dual mode constant voltage and constant current output. HLG-320H operates from 90 ~ 305VAC and offers models with different rated voltage ranging between 12V and 54V. Thanks to the high efficiency up to 94%, with the fanless design, the entire series is able to operate for -40°C ~ +90°C case temperature under free air convection. The design of metal housing and IP67/IP65 ingress protection level allows this series to fit both indoor and outdoor applications. HLG-320H is equipped with various function options, such as dimming methodologies, so as to provide the optimal design flexibility for LED lighting system.

Model Encoding



Type	IP Level	Function	Note
Blank	IP67	Io and Vo fixed	In Stock
Α	IP65	Io and Vo adjustable through built-in potentiometer	In Stock
В	IP67	3 in 1 dimming function (1~10VDC, 10V PWM signal and resistance)	In Stock
С		Terminal block for I/O connection. Output voltage and constant current level can be adjusted through internal potentiometer.	By request
D	IP67	Timer dimming function, contact MEAN WELL for details(safety pending).	By request




SPECIFICATION

MODEL		HLG-320H-12	HLG-320H-15	HLG-320H-20	HLG-320H-24	HLG-320H-30	HLG-320H-36	HLG-320H-42	HLG-320H-48	HLG-320H-54	
DC VOLTAGE		12V	15V	20V	24V	30V	36V	42V	48V	54V	
ОИТРИТ	CONSTANT CURRENT REGION Note.4		7.5 ~ 15V	10 ~ 20V	12 ~ 24V	15 ~ 30V	18 ~ 36V	21 ~ 42V	24 ~ 48V	27 ~ 54V	
	RATED CURRENT	22A	19A	15A	13.34A	10.7A	8.9A	7.65A	6.7A	5.95A	
	RATED POWER	264W	285W	300W	320.16W	321W	320.4W	321.3W	321.6W	321.3W	
								250mVp-p			
	RIPPLE & NOISE (max.) Note.2		150mVp-p	150mVp-p	150mVp-p	200mVp-p	250mVp-p	230111vp-p	250mVp-p	350mVp-p	
	VOLTAGE ADJ. RANGE				potentiometer)		22 - 201/	20 - 45\/	12 - 521/	40 - F0\/	
		10.8 ~ 13.5V		17 ~ 22V	21 ~ 26V	26 ~ 32V	32 ~ 39V	38 ~ 45V	43 ~ 52V	49 ~ 58V	
	CURRENT ADJ. RANGE	Adjustable for A/C-Type only (via built-in potentiometer) $11 \sim 22A$ $9.5 \sim 19A$ $7.5 \sim 15A$ $6.67 \sim 13.34A$ $5.35 \sim 10.7A$ $4.45 \sim 8.9A$ $3.8 \sim 7.65A$ $3.35 \sim 6.7A$ $2.97 \sim 5.95$									
	VOLTAGE TOLERANGE	11 ~ 22A	9.5 ~ 19A	7.5 ~ 15A				3.8 ~ 7.65A	3.35 ~ 6.7A	2.97 ~ 5.95	
	VOLTAGE TOLERANCE Note.3		±2.0%	±1.5%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	LOAD REGULATION	±2.0%	±1.5%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
		2500ms,80m		500ms,80ms/2	230VAC						
	HOLD UP TIME (Typ.)	15ms / 115VA	<u> </u>								
	VOLTAGE RANGE Note.5	90 ~ 305VAC 127 ~ 431VDC									
	TOLINOL NATIOE	(Please refer to "STATIC CHARACTERISTIC" section)									
	FREQUENCY RANGE	47 ~ 63Hz									
	DOWED EACTOR (Typ.)	PF≥0.98/115VAC, PF≥0.95/230VAC, PF≥0.94/277VAC @ full load									
INPUT	POWER FACTOR (Typ.)	(Please refer to "POWER FACTOR (PF) CHARACTERISTIC" section)									
	TOTAL HARMONIC DISTORTION	THD<20% (@ load≥50% / 115VAC,230VAC; @ load≥75% / 277VAC)									
	TOTAL HARMONIC DISTORTION	(Please refe	r to "TOTAL HA	ARMONIC DIS	STORTION (TH	D)" section)					
	EFFICIENCY (Typ.) (230Vac)	91%	92.5%	93.5%	94%	94%	94.5%	95%	95%	95%	
	EFFICIENCY (Typ.) (277Vac)	91.5%	93%	94%	94.5%	94.5%	95%	95%	95%	95%	
	AC CURRENT (Typ.)	3.5A / 115VA	C 1.65A/	230VAC	1.45A / 277VAC						
	INRUSH CURRENT(Typ.)	COLD START 70A(twidth=1010µs measured at 50% Ipeak) at 230VAC; Per NEMA 410									
	MAX. No. of PSUs on 16A										
	CIRCUIT BREAKER	1 unit (circuit breaker of type B) / 2 units (circuit breaker of type C) at 230VAC									
	LEAKAGE CURRENT	<0.75mA / 277VAC									
PROTECTION	OVER CURRENT Note.4	95 ~ 108% Constant current limiting, recovers automatically after fault condition is removed									
	SHORT CIRCUIT		<u> </u>		fault condition		J				
		14 ~ 17V	17.5 ~ 21V		27 ~ 33V	33 ~ 37V	40 ~ 46V	46.5 ~ 53V	53.5 ~ 60V	59 ~ 65V	
	OVER VOLTAGE						10 101	1000 000	1	100	
	OVER TEMPERATURE	Shut down and latch off o/p voltage, re-power on to recover Shut down and latch off o/p voltage, re-power on to recover									
	WORKING TEMP.						IRF" section)				
		Tcase= -40 ~ +90°C (Please refer to "OUTPUT LOAD vs TEMPERATURE" section) Tcase= +90°C									
ENVIRONMENT	MAX. CASE TEMP.		non-condensir	20							
	WORKING HUMIDITY			ig							
		-40 ~ +80°C, 10 ~ 95% RH									
	TEMP. COEFFICIENT	±0.03%/°C	,								
	VIBRATION		-		72min. each ald						
	SAFETY STANDARDS Note.8	UL8750(type"HL"), CSA C22.2 No. 250.0-08; TUV EN61347-1, EN61347-2-13 independent; IP65 or IP67 (except for HLG-320H C-type									
		J61347-1, J61347-2-13 (except for HLG-320H C-type) approved									
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC									
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH									
	EMC EMISSION Note.8	Compliance t	o EN55015, EN	155022 (CISPF	R22) Class B, E	N61000-3-2 C	lass C (@ load	d≧50%) ; EN6	31000-3-3		
	EMC IMMUNITY	Compliance t	o EN61000-4-2	2,3,4,5,6,8,11,	EN61547, EN5	5024, light indu	ustry level (sur	ge immunity Li	ne-Earth 4KV, I	Line-Line 2K'	
OTHERS	MTBF	157.1K hrs m	in. MIL-HDE	8K-217F (25°C)						
	DIMENSION	252*90*43.8r	nm (L*W*H)								
	PACKING	1.88Kg; 8pcs	16Kg/0.92CUF	T							
IOTE	 All parameters NOT specially mentioned are measured at 230VAC input, rated current and 25°C of ambient temperature. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 uf & 47 uf parallel capacitor. Tolerance: includes set up tolerance, line regulation and load regulation. Please refer to "DRIVING METHODS OF LED MODULE". De-rating may be needed under low input voltages. Please refer to "STATIC CHARACTERISTIC" sections for details. Length of set up time is measured at first cold start. Turning ON/OFF the driver may lead to increase of the set up time. The driver is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again. The model certified for CCC(GB19510.14, GB19510.1, GB17743 and GB17625.1) is an optional model. Please contact MEAN WELL for details. To fulfill requirements of the latest ErP regulation for lighting fixtures, this LED driver can only be used behind a switch without permanently 										
	connected to the mains. 10. This series meets the typic 11. Please refer to the warran		-	-		•	ly (tc) point (o	r TMP, per DL	.C), is about 75	5°C or less.	


■ BLOCK DIAGRAM

Fosc: 65KHz



■ DRIVING METHODS OF LED MODULE

X This series is able to work in either Constant Current mode (a direct drive way) or Constant Voltage mode (usually through additional DC/DC driver) to drive the LEDs.




Typical output current normalized by rated current (%)

In the constant current region, the highest voltage at the output of the driver depends on the configuration of the end systems.

Should there be any compatibility issues, please contact MEAN WELL.




■ DIMMING OPERATION




※ 3 in 1 dimming function (for B-Type)

- Output constant current level can be adjusted by applying one of the three methodologies between DIM+ and DIM-:
 1 ~ 10VDC, or 10V PWM signal or resistance.
- Direct connecting to LEDs is suggested. It is not suitable to be used with additional drivers.
- Dimming source current from power supply: $100\mu A$ (typ.)
- O Applying additive 1 ~ 10VDC




"DO NOT connect "DIM- to -V"

 \bigcirc Applying additive 10V PWM signal (frequency range 100Hz ~ 3KHz):





"DO NOT connect "DIM- to -V"


Applying additive resistance:



"DO NOT connect "DIM- to -V"












Note: In the case of turning the lighting fixture down to 0% brightness, please refer to the configuration as follow, or please contact MEAN WELL for other options.




Using a switch and relay can turn ON/OFF the lighting fixture.








※ De-rating is needed under low input voltage.



■ TOTAL HARMONIC DISTORTION (THD)


¾ 48V Model, Tcase at 80°C



■ EFFICIENCY vs LOAD


HLG-320H series possess superior working efficiency that up to 95% can be reached in field applications.

¾ 48V Model, Tcase at 80°C







■ LIFETIME














■ WATERPROOF CONNECTION

Waterproof connector

 $Water proof connector \ can be \ assembled \ on \ the \ output \ cable \ of \ HLG-320H \ to \ operate \ in \ dry/wet/damp \ or \ outdoor \ environment.$




Suitable Current

X Cable Joiner

Suitable Current

10A max.


10A max.



12A max

O CJ04 cable joiner can be purchased independently for user's own assembly. MEAN WELL order No.: CJ04-1, CJ04-2.

※ Junction Box Option



■ INSTALLATION MANUAL

Please refer to: http://www.meanwell.com/webnet/search/InstallationSearch.html