

Antenna cable - RAD-CAB-PFP400-80 - 2867393

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna cable, outside diameter: 10 mm (0.4 in.), inner conductor: solid, attenuation: 3.3 / 5.6 / 8.4 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2x N (male), cable length: 24 m (80 ft.)




Why buy this product

- Low attenuation
- UV resistant



Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 931766
GTIN	4017918931766

Technical data

Dimensions

Fixed cable length	24 m
External diameter	10.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Connection 1	Connector connection
Connection method	Type N (male)
Note	Both sides
Cable type	PFP-400
Outer sheath, material	PE
External sheath, color	black
Minimum bending radius	25.00 mm

Antenna cable - RAD-CAB-PFP400-80 - 2867393

Technical data

General

Frequency range	400 MHz ... 5.8 GHz
Impedance	50 Ω

Attenuation

868 / 900 MHz	3.3 dB
2.4 GHz	5.6 dB
5 GHz	8.4 dB

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>