

Cable - CABLE-FCN40/1X50/ 1,0M/IP/MEL - 2903477

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Round cable set; controller: Mitsubishi Electric MELSEC L, MELSEC Q, Honeywell MasterLogic ML200; connection 1: Fujitsu connector (1x 40-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 1 m

Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4046356743280

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. total current of all branches	2 A
Max. conductor resistance	0.16 Ω /m
Length of cable	1 m
Single wire, cross section	0.14 mm ²
Single wire, cross section [AWG]	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	8.7 mm
Shielding	no
Outer sheath, material	PVC
External sheath, color	RAL7035

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Cable - CABLE-FCN40/1X50/ 1,0M/IP/MEL - 2903477

Technical data

Environmental conditions

Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1
Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	against occasional splashes

Connector 1

Connection name	Field level
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Connector 2

Connection name	Controller level
Connection method	Fujitsu connector
Number of connections	1
Number of positions	40

Supported controller

Controller	MITSUBISHI MELSEC Q
- suitable I/O card	QX71
	QX72
	QX82
	QX82-S1
Controller	MITSUBISHI MELSEC L
- suitable I/O card	LX41C4
	LX42C4
Controller	Honeywell MasterLogic 200
- suitable I/O card	2MLI-D24A
	2MLI-D28B
	2MLF-SOEA

Standards and Regulations

Standards/regulations	DIN EN 60352-4
	DIN EN 60603-1
Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1
Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	against occasional splashes

Color code

Connector 1 = connector 2 (optional) = wire color	Fujitsu40 (B1) = IDC/FLK50 (11) = black
	Fujitsu40 (B2) = IDC/FLK50 (48) = brown

Cable - CABLE-FCN40/1X50/ 1,0M/IP/MEL - 2903477

Technical data

Color code

	Fujitsu40 (A5) = IDC/FLK50 (46) = red
	Fujitsu40 (B5) = IDC/FLK50 (22) = orange
	Fujitsu40 (A6) = IDC/FLK50 (45) = yellow
	Fujitsu40 (B6) = IDC/FLK50 (21) = green
	Fujitsu40 (A7) = IDC/FLK50 (44) = blue
	Fujitsu40 (B7) = IDC/FLK50 (20) = violet
	Fujitsu40 (A8) = IDC/FLK50 (43) = gray
	Fujitsu40 (B8) = IDC/FLK50 (19) = white
	Fujitsu40 (A9) = IDC/FLK50 (42) = white-black
	Fujitsu40 (B9) = IDC/FLK50 (18) = white-brown
	Fujitsu40 (A10) = IDC/FLK50 (41) = white-red
	Fujitsu40 (B10) = IDC/FLK50 (17) = white-orange
	Fujitsu40 (A11) = IDC/FLK50 (40) = white-yellow
	Fujitsu40 (B11) = IDC/FLK50 (16) = white-green
	Fujitsu40 (A12) = IDC/FLK50 (39) = white-blue
	Fujitsu40 (B12) = IDC/FLK50 (15) = white-violet
	Fujitsu40 (A13) = IDC/FLK50 (34) = white-gray
	Fujitsu40 (B13) = IDC/FLK50 (10) = brown-black
	Fujitsu40 (A14) = IDC/FLK50 (33) = brown-red
	Fujitsu40 (B14) = IDC/FLK50 (9) = brown-orange
	Fujitsu40 (A15) = IDC/FLK50 (32) = brown-yellow
	Fujitsu40 (B15) = IDC/FLK50 (8) = brown-green
	Fujitsu40 (A16) = IDC/FLK50 (31) = brown-blue
	Fujitsu40 (B16) = IDC/FLK50 (7) = brown-violet
	Fujitsu40 (A17) = IDC/FLK50 (30) = brown-gray
	Fujitsu40 (B17) = IDC/FLK50 (6) = brown-white
	Fujitsu40 (A18) = IDC/FLK50 (29) = green-black
	Fujitsu40 (B18) = IDC/FLK50 (5) = green-brown
	Fujitsu40 (A19) = IDC/FLK50 (28) = green-red
	Fujitsu40 (B19) = IDC/FLK50 (4) = green-orange
	Fujitsu40 (A20) = IDC/FLK50 (27) = green-blue
	Fujitsu40 (B20) = IDC/FLK50 (3) = green-violet

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Cable - CABLE-FCN40/1X50/ 1,0M/IP/MEL - 2903477

Approvals

Approvals

EAC / UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

EAC			RU C- DE.A*30.B00767
-----	--	--	-------------------------

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	

cULus Listed			
--------------	--	--	--

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>