

# Termination resistor - SAC-4P-M12MS CCL TR - 1558470


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



CC-Link termination resistor, 4-pos., M12 plug



## Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 293648
GTIN	4046356293648

## Technical data

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
Degree of protection	IP65
	IP67

### General

Rated current at 40°C	20 mA
Rated voltage	24 V
Termination resistor	110 Ω (Contact 2 and 4)
Power consumption	0.5 W
Number of positions	4
Color handle area	black
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Status display	No
Overvoltage category	II
Degree of pollution	3
Insertion/withdrawal cycles	≥ 100

### Material

# Termination resistor - SAC-4P-M12MS CCL TR - 1558470

## Technical data

### Material

Flammability rating according to UL 94	HB
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

### Characteristics head 2


Color	black
-------	-------

### Standards and Regulations

Flammability rating according to UL 94	HB
----------------------------------------	----


## Drawings

Schematic diagram




Pin assignment M12 plug, 4-pos., A-coded, view plug side

Dimensional drawing



M12 termination resistor

Circuit diagram



CC-Link termination resistor, R = 110 Ω

## Approvals

### Approvals

# Termination resistor - SAC-4P-M12MS CCL TR - 1558470

## Approvals

Approvals


EAC

---

Ex Approvals

---

## Approval details

EAC		EAC-Zulassung
-----	-----------------------------------------------------------------------------------	---------------

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>