

### Main

Product or component type	Surge protection device
Range of product	Surgelogic
Device short name	EMA

### Complementary

Surge current	240 kA per phase
System Voltage	120/240 V AC
Phase	1 phase
Wiring configuration	3-wire
[Uc] maximum continuous operating voltage	150 V
Nominal discharge current	20 kA
Short-circuit protection	200 kA
Local signalling	Status LED, green = normal operation per phase Status LED, red = fault per phase
Provided equipment	Switch-disconnector with integrated switch for off/on/automatic Alarm enable/disable switch Sine wave tracking module
Mounting location	Service entrance
Device mounting	Surface Flush

### Environment

NEMA degree of protection	NEMA 1/12/3R
enclosure material	Painted sheet steel, colour : grey
standards	ANSI/IEEE C62.41 ANSI/IEEE C62.45 UL Category Section 37.3 UL 1283 ed. 5 UL 1449 type I ed. 3

### Offer Sustainability

Not Green Premium product	Not Green Premium product
Will be Compliant on 4Q2016	Will be Compliant on 4Q2016 Will be Compliant on 4Q2016

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.