







APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A		REDRAWN	11/18/13	KM/TW
B		REDRAWN	2/10/15	HR/NP
C		REVISED SPEC.	7/15/15	HR/YC



SPECIFICATIONS:
 Material: _____
 Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
 Insulator color: Natural
 Contacts: Brass
 Solder nail: Brass
 Plating: _____
 Tin over Nickel underplate overall

Electrical:
 Current rating: 1 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 100 Mohms min
 Dielectric withstanding voltage: 250 VAC for 1 minute
 Temperature Rating: _____
 Operating temperature: -40°C to +85°C
 Environmental: _____
 Lead free, RoHS compliant.

PACKAGED ON TAPE & REEL



Positions: 02 thru 15
 A = .049 [1.25] x No. of Spaces
 B = .049 [1.25] x No. of Spaces + .118 [3.00]
 C = .049 [1.25] x No. of Spaces + .071 [1.80]
 D = .049 [1.25] x No. of Spaces + .230 [5.85]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE IN INCHES [MM]
 TOLERANCES EXCEPT AS NOTED
 INCHES Holes
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

ADAM TECH
 909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN	BW	01/17/07	12SSH-B-XX-TR-SMT-T/R	C
CHECKED				
APPROVED				

REF: S00124T SCALE: NTS SHEET 1 OF 1