

COLORS AND LIGHTS UNDER YOUR CONTROL

# ZigBee Lighting Controller ON/OFF & 0(1)-10V Dimming

# **Product Features**

- ZigBee Wireless Control of Luminaires
- +20dBm ZigBee transmit power
- ON/OFF and 0(1)-10V Analog Dimming Control, 100mA Sink
- Compatible with LED Drivers and Electronic Ballasts & that comply with IEC60929 Annex E2, 1-10V Dimming.
- ON/OFF AC switching up to 277Vac
- Stores last dim setting even when powered off.

## **Safety and Compliance**

- 1. UL8750, CSA 22.2 safety compliant, UL2043 Plenum Rated
- 2. FCC, 47CFR Part 15 Class B compliant
- 3. ZigBee HA Certified
- 4. Compact, Lightweight.
- 5. US Patent Pending
- 6. EN61000-4-5: 2kV L-N, 8/20 µsec surge protection.

### **Environmental**

- 1. Operating temperature: Tc Maximum 72 °C, Ambient -5 to +50 °C Max.
- Storage temperature range: -40 to +80°C
- 3. Humidity (non-condensing): 5% 95%RH
- 4. Cooling: Convection
- 5. Vibration Frequency: 5-55Hz/2g, 30 minutes
- 6. Impact resistance: 1g/s

# Electrical Specifications at 25°C

- Input voltage range: 100-277Vac
- Frequency: 47 63HZ
- AC Relay Resistive Switched Current: ≤9A<sup>(1)</sup>
- AC Relay Inrush Current: <60A
- Input current Module Power: ≤0.05A for Units power use
















Part	Num	bers
I GIL	ITUIT	DC13

Part Number	Dimming US Class 2	Dimming CN Class 2	Control	ON/OFF Control	0(1)-10V Analog	AC Relay Voltage Range	AC Relay Maximum Current
LCM-1C09-ZB	YES	YES	ZigBee HA	YES	YES	100-277Vac	9A

# **Typical Application Circuit**

# LCM-1C09-ZB



VIOLET (0-10V) Analog+ Dim Control

## (1) Max Rated AC Relay Loads (RED Wire):

LED Driver, Electronic Ballast, Incandescent & Inductive Load: 1200W @ 277VAC, 1000W @ 208-240VAC, 800W @ 120VAC


AC Resistive Load: 100-277Vac 50/60Hz, 9A Maximum.

# **ZigBee Lighting Controller** ON/OFF & 0(1)-10V Dimming

# **Mechanical Dimensions: Inches [mm]**

Material: Gray 5VA PC ABS Plastic Case Weight: 105 Grams (3.7 oz.) Typical

# Labeling Example ZigBee HA Wireless Lighting Controller EuControls Corp. Www.EuControls.com ACINPUT La BLACK N = WHITE RED SWITCHED 100-277Vac 1-10V DIM OUTPUT DIM+ = PURPLE DIM+ = PURPLE DIM+ = PURPLE DIM+ = GRAP Made in China Labeling Example ZigBee HA Wireless Lighting Controller EuControls Corp. Www.EuControls.com Part Number: LCM-1C09-ZB Input Voltage: 100 - 277VAC 50/60Hz Input Current: 9.05 Amp Max Switched Output: Fluorescent, Incan, LED 120Vac: 800W Max, 208-240Vac 1000W Max 1-10V Dim Output DIM+ = GRAP 1-10V Sink Dimming Output, @ 100mA Sink 1-10V Output is UL & cUL Class 2 HG REV A1





# **ZigBee Lighting Controller** ON/OFF & 0(1)-10V Dimming

# **Input Specifications**

Parameter	Min.	Тур.	Max.	Notes/Conditions
Input Voltage	90 Vac		277 Vac	120, 230, 240, 277 Vac Nominal Values
Input Frequency	47 Hz		63 Hz	50/60Hz Nominal
Relay AC Current			9.0 A	Measured at 120Vac/60Hz Input
Relay Inrush Current (Peak)			60A	Measured at 277Vac/60Hz Input
Relay Inrush Current (I <sup>2</sup> t)			1.35 A <sup>2</sup> s	50% Ipeak duration ∼750 µsec (1/2*Ip²*t)
ZigBee Control Transmit Power			+20dBm	ON/OFF and 0-10V dimming, Standard ZigBee

## **Output Specifications**

Parameter	Min.	Тур.	Max.	Notes/Conditions
AC Relay Switch ON/OFF (Vac)	0		277Vac	Isolated Relay N/O Contacts
AC Relay Load @120VAC (W)	0		800W	Fluorescent, LED Drivers, Incandescent & Inductive Loads
AC Relay Load @ 208-240Vac (W)	0		1,000W	Fluorescent, LED Drivers, Incandescent & Inductive Loads
AC Relay Load @ 277Vac (W)	0		1,200W	Fluorescent, LED Drivers, Incandescent & Inductive Loads
AC Relay Load Resistive (A)	0		9A	Resistive Loads
Sink Current on 0-10V (+) Purple Wire	0mA		100mA	IEC60929 Annex E2
Absolute Voltage Range on 0-10V (+) Purple Wire	-20.0V		+20V	IEC60929 Annex E2
Dimming Range	0.9V		+20V	Ballast or Led Driver provides Dim Voltage & Current per IEC60929 Annex E2, 0(1)-10V Analog Dimming

# **Environmental Specifications**

Parameter	Min.	Тур.	Max.	Notes/Conditions
Case Temperature (Tc)			+72 °C	Measured at location specified on case.
Operating Temperature (Ta)	-5 °C		+50 °C	Operating temperature range.
Storage Temperature (Ts)	-40 °C		+85 °C	Non operating temperature range.
Operating Humidity			95% RH	Relative Humidity, non-condensing.
Vibration	5 Hz		55 Hz	2G, 10 minutes/1 cycle, period 30 minutes, each along X, Y, Z axis.

# Safety & EMC Compliance

Safety	Notes/Standards				
UL/CUL	UL8750 & CAN/CSA C22.2 No. 250.13, UL2043 Plenum Rated				
CE	EN61347-1, EN61347-2-13				
Withstand Voltage Relay	Input to Output Across Relay Contacts: 700 Vac				
Withstand Voltage AC In to Dim Out	Input to DIM: >1750 Vac				
Dimming Circuit	UL & cUL Isolated Class 2, Dim+ Purple/Dim- Gray				
FCC	Compliant Class B				
EN 61000-4-5	Part 4-5: Surge Immunity test, 2 kV L-N				

# **ZigBee Lighting Controller** ON/OFF & 0(1)-10V Dimming



