

Interface module - VIP-2/PT/D15SUB/F - 2903780

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with push-in connection and D-SUB miniature socket strip, for mounting on NS 35 rails, 15-pos.

The illustration shows a 15 position version with male D-sub connector.



Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4046356796552

Technical data

Dimensions

Width	46.9 mm
Height	72.1 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. perm. operating voltage	25 V AC
	60 V DC
Max. perm. current (per branch)	2 A
Number of positions	15
Status display	No
Mounting position	any

Connection data for connection 1

Connection name	Field level
-----------------	-------------

Interface module - VIP-2/PT/D15SUB/F - 2903780

Technical data

Connection data for connection 1

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB socket strip
Number of connections	1
Number of positions	15

Standards and Regulations


Connection in acc. with standard	CSA
Standards/regulations	IEC 60664
	DIN EN 50178
Rated surge voltage	1.2 kV
Degree of pollution	2
Overvoltage category	II

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Circuit diagram



Approvals

Approvals

Approvals


CSA / UL Recognized / cUL Recognized / EAC / CSAus / cULus Recognized


Interface module - VIP-2/PT/D15SUB/F - 2903780


Approvals

Ex Approvals


Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	2122203
mm ² /AWG/kcmil		26-14	
Nominal current I _N		2 A	
Nominal voltage U _N		105 V	

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
mm ² /AWG/kcmil		26-14	
Nominal current I _N		2 A	
Nominal voltage U _N		125 V	

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
mm ² /AWG/kcmil		26-14	
Nominal current I _N		2 A	
Nominal voltage U _N		125 V	

EAC			RU C- DE.A*30.B.01742
-----	---	--	--------------------------

CSAus		http://www.csagroup.org/services-industries/product-listing/	2122203
mm ² /AWG/kcmil		28-14	
Nominal current I _N		2 A	
Nominal voltage U _N		105 V	

Interface module - VIP-2/PT/D15SUB/F - 2903780

Approvals

cULus Recognized



<http://www.csagroup.org/services-industries/product-listing/>

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>