PLCC4 SMD Top View Package LED SMTL4-SRGY, RED/GREEN/YELLOW




SMTL4-SRGY

- Industry Standard PLCC4 Footprint
- 3 Super Bright Chips in One Low Profile Package
- High Luminous Intensity
- Wide Viewing Angle
- High Power Efficiency



Bivar SMTL4 Super Bright Tri-Color LED combines three chips in a single package and is offered in an industry standard PLCC4 footprint. The SMTL4 LED has a water clear lens for high luminous intensity and wide viewing angle making them ideal for outdoor illumination applications where higher ambient lighting conditions exist. The flexible three chip design allows for a wide variety of lighting options where the chips can be individually driven or mixed to create different color combinations. The robust package is ideal for harsh working environments and can be clustered in LED arrays for high luminous applications. Low power consumption and excellent long life reliability are suitable for battery powered equipment. Bivar SMTL4 LED is packaged in standard tape and reels for pick and place assemblies.

Part Number	Material	Emitted Color	Lumen Typ. mcd	Lens Color	Viewing Angle	
SMTL4-SRGY	AlGaInP	Red	180			
	InGaN	Green	1450	Water Clear	120°	
	AlGaInP	Yellow	180			



Outline Dimensions

All dimensions are in inches [millimeters].
Standard tolerance: ±0.010" unless otherwise noted



Bivar reserves the right to make changes at any time without notice



Absolute Maximum Ratings

 $T_A = 25^{\circ}C$ unless otherwise noted

Power Dissipation	Red, Yellow - 78 mW Green - 78 mW
Continuous Forward Current	Red, Yellow - 30 mA Green - 30 mA
Peak Forward Current ¹	100 mA
Reverse Voltage	5 V
Electrostatic Discharge Classification (HBM)	2000 V
Derating Linear From 25°C	0.4 mA/°C
Operating Temperature Range	-40 ~ +85°C
Storage Temperature Range	-40 ~ +100°C
Soldering Temperature ²	260°C

Notes: 1. 10% Duty Cycle, Pulse Width ≤ 0.1 msec.

2. Solder time less than 5 seconds at temperature extreme.

Electrical Characteristics

 $T_A = 25^{\circ}C \& I_F = 20 \text{ mA}$ unless otherwise noted

Emitting Color	-	ward ge (V) ¹	Recommend Forward Current (mA)	Reverse Current (μΑ) V _R =5V	Dominant Wavelength (nm) ²	Lumi Intensity	nous y (mcd) ³	Viewing Angle 2 ⊖ ½ (deg)
	TYP	MAX	ТҮР	MAX	ТҮР	MIN	TYP	TYP
Red	1.9	2.6	20	10	625	115	180	
Green	3.3	4.5	20	10	525	1050	1450	120
Yellow	1.9	2.4	20	10	591	115	180	


Notes: 1. Tolerance of Forward Voltage : ±0.05V.

2. Tolerance of Dominant Wavelength : ±0.1nm.

3. Tolerance of Luminous Intensity : ±15%.

Directivity Radiation

 $T_A = 25^{\circ}C$ unless otherwise noted



Bivar reserves the right to make changes at any time without notice.



Typical Electrical / Optical Characteristics Curves

 $T_A = 25^{\circ}C$ unless otherwise noted




Fig.1 Relative Luminous Intensity vs. Wavelength

Relative Luminous Intensity I_v/I_v (20 mA) = f (I_F) $T_A = 25^{\circ}C$

Ambient Temperature vs. Allowable Forward Current





Fig.2 Relative Luminous Intensity vs. Forward Current








Bivar reserves the right to make changes at any time without notice.

PLCC4 SMD Top View Package LED SMTL4-SRGY, RED/GREEN/YELLOW




Recommended Soldering Conditions



Tape and Reel Dimensions


Note: 2000 pcs/Reel



Bivar reserves the right to make changes at any time without notice

PLCC4 SMD Top View Package LED SMTL4-SRGY, RED/GREEN/YELLOW






Outline Drawings Notes:

All dimensions are in inches [millimeters].
Standard tolerance unless otherwise noted: X.XXX ± 0.010"

X.X ± 0.01 X.X ± 0.1

Packaging and Labeling Plan

Note: 1 Reel / Bag



Part No.	XXXX-XXX-XXX
Prod. No.	XXXX-XXX-XXX
PO No.	XXXX
Lot No.	XXXXXXXXXX
Q'ty:	X.XXX PCS
Q.C.	XXX BIN
Date:	2008.XX.XX

Internal Quality Control Label

Bivar. Inc.	MSL4
4 Thomas, Irvine, CA 92618	-2593
LOT: XXX.XXXXX.XX	
Part: XXXX-XXX-X	XX
Quantity: X.XXX	RoHS Compliant

Bivar Standard Packaging Label

Bivar reserves the right to make changes at any time without notice.