



Main

Range	Thalassa
Product name	Thalassa PLA
Device application	Multi-purpose
Product or component type	Suitable enclosure
Device short name	PLAT
Enclosure nominal height	49.21 in (1250 mm)
Enclosure nominal width	49.21 in (1250 mm)
Enclosure nominal depth	12.6 in (320 mm)
Enclosure mounting	Floor-standing
Device composition	1 canopy 2 rear panel 2 door 2 side part 1 top part 1 bottom part

Complementary

Body type	Open top and sealed bottom part assembled with side parts
Door type	Plain front
Number of doors	2
Door opening side	Right and left 120 °
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Front Rear Top
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7032
Standards	IEC 62208
Product certifications	Veritas

Environment

IP degree of protection	IP44 with ventilated canopy IEC 60529
IK degree of protection	IK10 plain door IEC 62262
fire resistance	1760 °F (960 °C) IEC 62208
ambient air temperature for storage	-31...194 °F (-35...90 °C)

Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 0940 - Schneider Electric declaration of conformity	Compliant - since 0940 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations

Contractual warranty

