



Main

| | |
|---------------------------|--|
| Range | Thalassa |
| Product name | Thalassa PLA |
| Device application | Multi-purpose |
| Product or component type | Suitable enclosure |
| Device short name | PLAT |
| Enclosure nominal height | 59.06 in (1500 mm) |
| Enclosure nominal width | 19.69 in (500 mm) |
| Enclosure nominal depth | 12.6 in (320 mm) |
| Enclosure mounting | Floor-standing |
| Device composition | 1 canopy 1 door 1 rear panel 2 side part 1 top part 1 bottom part |

Complementary

| | |
|-----------------------------|--|
| Body type | Open top and sealed bottom part assembled with side parts |
| Door type | Plain front |
| Number of doors | 1 |
| Door opening side | Reversible 120 ° |
| Lock type | 4 points lock, handle with 5 mm double bar insert |
| Accessibility for operation | Front Rear Top |
| Removable parts | Door by hinges Rear panel by fixing element Canopy by fixing element |
| Material | Polyester reinforced with fibreglass |
| Colour | Grey RAL 7032 |
| Standards | IEC 62208 |
| Product certifications | Veritas |

Environment

| | |
|-------------------------------------|---------------------------------------|
| IP degree of protection | IP44 with ventilated canopy IEC 60529 |
| IK degree of protection | IK10 plain door IEC 62262 |
| fire resistance | 1760 °F (960 °C) IEC 62208 |
| ambient air temperature for storage | -31...194 °F (-35...90 °C) |

Offer Sustainability

| | |
|---|---|
| Green Premium product | Green Premium product |
| Compliant - since 0940 - Schneider Electric declaration of conformity | Compliant - since 0940 - Schneider Electric declaration of conformity |
| Reference not containing SVHC above the threshold | Reference not containing SVHC above the threshold |
| Available | Available |
| Need no specific recycling operations | Need no specific recycling operations |

Contractual warranty

