




## 4 IN. OCTAGON DRAWN BOXES & EXTENSION RINGS WITH CONDUIT KO'S

4 in. Octagon Box, 1-1/2" Deep - Drawn with Conduit KO's, Raised Ground

A38



Catalog #: 127

### APPLICATIONS

RACO® Octagon Boxes are used in the installation of ceiling or wall lighting fixtures  
N/A

### PRODUCT FEATURES

Combination screw heads provide for faster installation

### UL LISTED

File E195978

### COMPLIANCES

MSDS  
[www.hubbell-rtb.com/certifications/Hubbell-RACO\\_MSDS\\_for\\_Steel\\_Boxes\\_and\\_Covers.pdf](http://www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf)

### FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit  
Country of Origin: USA

### RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No  
Fixture (Static) Lbs.: 50

### CONFIGURATION

Bracket Type: No Bracket  
Drawn or Welded: Drawn  
Raised Ground: Yes  
Side Knockout(s): (2) 1/2 in. & (2) 3/4 in.  
Bottom Knockouts(s): (2) 1/2 in. & (2) 3/4 in.

### DRAWING DIMENSIONS

Dimension A: 1-1/2 in.  
Dimension B: 4 in.

### PRODUCT MEASUREMENTS

Depth: 1-1/2 in.  
Cubic Inches (cm3): 15.5 (254.0)  
Wt. Ea. (Lbs.): 0.508  
Product Length (in.): 1.56  
Product Width (in.): 4.00  
Product Height (in.): 4.00

### PACKAGING

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 50.80  
Ship Carton Length (in.): 16.50  
Ship Carton Width (in.): 5.38  
Ship Carton Height (in.): 7.50  
Ctn Weight (Lbs.): 12.70  
Pallet Qty: 2800  
UPC Number: 050169001271  
I2of5: 40050169001279