

## EUPS10012

### Power Supply

#### Product Features


- Switch mode power supply: 100VAC - 240VAC input, 12VDC stabilized output, 8.33Amp rated.
- Meets RoHS lead free requirements.
- Over-voltage, over-current, and short-circuit protection.
- High efficiency, low operating temperature.
- FCC, 47CFR Part 15 Class B compliant.
- UL/cUL Listed.

#### Product Specifications


- |                         |                                                            |
|-------------------------|------------------------------------------------------------|
| • Input Voltage         | 100VAC - 240VAC                                            |
| • Output Voltage        | 12VDC                                                      |
| • Output Current        | 0 - 8.33Amp                                                |
| • Output Power          | 100Watts                                                   |
| • Ripple & Noise        | 100mV Max                                                  |
| • Operating Temperature | 0°C ~ 40°C                                                 |
| • Storage Temperature   | -20°C ~ 85°C                                               |
| • Operating Humidity    | 5% ~ 95% (non condensing)                                  |
| • Size                  | (L)156 x (W)67 x (H)40 (mm)<br>6.14 x 2.64 x 1.57 (inches) |
| • Length of AC Wire     | (L)1200 (mm) or 47 (inches)                                |
| • Length of DC Wire     | (L)1500 (mm) or 59 (inches)                                |
| • Weight                | 480g                                                       |



#### Dimensions



AC Power Cable 1200 mm (47 inches)



1500 mm (59 inches) DC Power Cable

