

HMI5070L

**CLASS I
DIVISION 2**

**UL US
LISTED**

CE

**RoHS
Compliant**

NEMA4X



7" Slimline Industrial HMI

- Ultra-slim form factor
- 16 million color TFT display
- Moisture-resistant PCB coating
- Analog resistive touchscreen
- 800 x 480 resolution
- 32 Bit RISC CPU, 600MHz
- 128MB flash memory, 128MB RAM
- Built-in Ethernet
- 2 serial ports and 1 USB host port
- Isolated power supply
- Two year warranty

Ultra-slim form factor, sleek aesthetic and affordable price point make the HMI5070L the perfect choice when you need a high-quality, value-priced HMI.

The Maple Systems HMI5070L is a slim-form operator interface with a bright 800 x 480 pixel touchscreen display, a high speed 600MHz microprocessor and 128MB of memory for complex and graphic intensive projects.

The ultra-thin form factor of the HMI5070L makes mounting in tight spots easy, the fanless design requires no extra space for cooling. The HMI5000 Series is also NEMA4X/IP65 rated, allowing for peak performance in adverse conditions.

With our EZWarePlus software package, you can configure the HMI5070L to your exacting specifications. The extensive

features of the software include alarm management, batch recipes, BACnet for building automation and control networks and much more - all making your operator interface a more integral part of your automation control system.

Maple Systems stands behind your HMI product with a two-year warranty, complimentary technical support, an online support center, and numerous online instructional videos.



10" HMI5100L

7" HMI5070L

**Every Machine
Needs the
Human Touch**



www.maplesystems.com

HMI5070L Specifications

Hardware

CPU Type	32-bit RISC CPU, 600MHz
Memory	128MB Flash, 128MB RAM
SD Card Slot	N/A
Ethernet Port	10/100 Base-T (RJ45)
Serial Ports	Com1: RS-232/RS-485, 2 or 4 wire Com3: RS-485, 2 wire
Audio	N/A
USB Ports	1 host 2.0 port
RTC	Built-in

Display

Type	7.0" TFT color
Size (WxH)	6.10 x 3.40 inches [155 x 86mm] 7" diagonal
Resolution (pixels)	800 x 480
Brightness (cd/m ²)	350
Contrast Ratio	500:1
Max Colors	16 million
Viewing Angle (°)	60/70/70/70 (T,B,R,L)
Backlight	LED
Backlight Longevity	30,000 hrs.

Specifications subject to change without notice.

Touchscreen

Type	4-wire analog resistive
Resolution	Continuous
Light Transmission	Above 80%
Lifespan	1 million activations minimum

Environmental

Operating Temperature	32 ~ 122°F (0 ~ 50°C)
Storage Temperature	-4° ~ 140°F (-20 ~ 60°C)
Relative Humidity	10% ~ 90% (non-condensing)
Shock (operation)	10 to 25Hz (X,Y,Z direction, 2G, 30 minutes)
Ratings	IP65, NEMA 4X compliant front panel
Certifications	Class I, Division 2, cULus, CE, RoHS


Mechanical

Enclosure	Plastic molding
Dimensions (WxHxD)	7.89 x 5.76 x 1.34 inches [200 x 146 x 34mm]
Panel Cutout Dim. (WxH)	7.56 x 5.43 inches [192 x 138mm]
Weight	1.31 lbs [.6kg]
Mounting	Panel mount
Power Requirements	24VDC, 350mA nominal
Warranty	2 years


Order Number

HMI5070L	7.0" Slim Graphic HMI
----------	-----------------------

Dimensions



Front View



Rear View

- A Fuse
- B Power Connector
- C DIP Switch & Reset Button
- D Com1, Com3 RS485
- E USB Host port
- F Com1, RS232
- G Ethernet Port 10/100

Dimensions in inches [mm]



Bottom View

Maple Systems, Inc.

808 134th St SW, Suite 120, Everett, WA 98204

425.745.3229 • 425.745.3429 (fax) • Email: maple@maple-systems.com • www.maplesystems.com