

Starter kit - ILC 131 STARTERKIT - 2701835

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



ILC 131 starter kit incl. ILC 131 ETH, control panel, power supply unit, plus accessories and cables with test application set up

Product Description


Test the highly communicative ILC 131 ETH high-performance controller. Small to medium function units can be automated inexpensively using this high-performance controller. The high-performance controller features modular expansion, easy programming, and high performance. We have compiled this starter kit so that you can try out the capabilities of the ILC 131 ETH for yourself. It has digital and analog output and input terminals as well as simulation modules. In addition, example projects for PC WORX EXPRESS and the web server are available to the user.

Why buy this product

- ✓ Integrated I/Os: 8/4
- ✓ Processing time per 1000 instructions: 90 µs (bit data types), 1.7 ms (mixed data types)
- ✓ Program/mass storage: 192 KB/192 KB
- ✓ Retentive mass storage: 8 KB
- ✓ Supply voltage: 24 V DC



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 858588
GTIN	4046356858588

Technical data

Environmental Product Compliance

REACH SVHC	1,2-dimethoxyethane,ethylene glycol dimethyl ether (EGDME) 110-71-4
	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Starter kit - ILC 131 STARTERKIT - 2701835

Articles in set

Controller - ILC 131 ETH - 2700973



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Inline ME terminal - IB IL AI 2/SF-ME - 2863944



Inline, Analog input terminal, Analog inputs: 2, 0 V ... 10 V, -10 V ... 10 V, 0 mA ... 20 mA, 4 mA ... 20 mA, -20 mA ... 20 mA, connection method: 2-wire, transmission speed in the local bus: 500 kbps, including Inline connector and labeling field

Interface module - UM 45-IB-DI/SIM8 - 2962997



VARIOFACE switch module, with COMBICON connector, for simulation, for 8 signals, for mounting DIN rail NS 35

Software - PC WORX EXPRESS - 2988670



PC WORX EXPRESS is a piece of easy-to-operate engineering software. Class 100 and class 1000 modular small-scale controllers as well as the PC WORX SRT software controller with IEC-61131 programming languages ST and LD are supported. Free programming version without licensing mechanism, max. 128 kbyte of input and output data.

Approvals

Approvals

Approvals


EAC

Ex Approvals

Approval details

Starter kit - ILC 131 STARTERKIT - 2701835

Approvals

EAC		EAC-Zulassung
-----	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>