

PNOZ s6.1 48-240VACDC 3 n/o 1 n/c

750156



PNOZsigma safety relay (standalone), two-hand control relay, inputs: Per pushbutton 1 N/O, 1 N/C, outputs: 3 N/O, 1 N/C, 1 SC, UB =48 - 240 V AC/DC, width: 22.5 mm, plug-in screw terminals, simultaneity monitoring with two-hand pushbutton.

## Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, KOSHA, TÜV, EAC (Eurasian)
Technical data	
Electrical data	
Supply voltage (V):	48 - 240 V
Type of supply voltage U1:	AC/DC
Power consumption AC:	7 VA
Power consumption DC:	3.5 W
Max. device circuit breaker:	Max. conductor cross section
Type of two-hand device:	III A
Inputs	
Number of inputs:	2
Semiconductor outputs	
Number of semicond. outputs:	1
Utilisation cat. to EN 60947-1:	DC-12
Relay outputs	
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	6 A
Voltage DC1 safety cont.:	24 V

Max. current DC1 safety cont.:	6 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	3 A
Voltage DC13 safety cont.:	24 V
Safety contacts: AC at UL:	240 VAC G.U. (same polarity)
Relay contact material:	AgCuNi
Addit. contact details relay:	+ 0.2 µm Au
<b>Environmental data</b>	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-10 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61000-6-4, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	2
<b>Mechanical data</b>	
Mounting position:	any
Housing material lower section:	PC
Housing material front plate:	PC
Housing material upper part:	PC
Connection terminal:	Screw terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	24 - 12 AWG
Height dimension:	98 mm
Width dimension:	22.5 mm
Depth dimension:	120 mm

Net weight:	205 g
Gross weight:	215 g
<b>Environment</b>	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
<b>Commercial data</b>	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27371821
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001452

## Optional accessories

750010

PNOZ s terminator plug ( 10 pieces)



750004

PNOZ s Setscrew terminals 22,5mm

