## Power-Sonic Batteries Engineered With Vision. Built With Care.



Power-Sonic Corporation has been a leading force since 1970 in the supply of high quality cost effective batteries.


We market an extensive range of rechargeable batteries worldwide. These batteries envelop a broad spectrum of electronic and industrial applications, either as the prime or standby power source.

Power-Sonic is dedicated to continual product development to improve the performance and reliability of our product range. New batteries are constantly being introduced to meet the ever evolving needs of industry.


We are a 100% US owned private company. The corporation has an enviable record of growth and financial stability.

Providing our customers with reliable, yet economical, products is the corner stone of the Power-Sonic mission.

## Terminals: (mm)



## **Physical Dimensions: in (mm)**



## About Lithium Iron Phosphate (LiFePO<sub>4</sub>)

- Compact and only 40% of the weight of comparable capacity SLA batteries. Making it much easier to handle and transport.
- Extraordinary cycle life ~ 2,500 cycles.
- 2 ½ hours recharge time with 20A current charge.
- Integrated battery
  management system
  (BMS) controls the
  parameters of the battery
  to provide optimum
  safety and performance.
  Among other functions,
  the BMS balances the
  battery cells and protects
  against overcharging or
  overdischarging.
- Safe and stable chemistry. The use of lithium iron phosphate greatly reduces the risk of combustion or explosion due to high impact, overcharging or short circuit situations.

- The battery will communicate with most smart charging (power module) systems.
- The SMbus provides access to a battery history log.
- Rugged plastic case and cover, flame retardant (FR) to UL94 V-O.
- The battery cells are manufactured with internationally patented lithium iron phosphate powder from Phostech, Canada.
- UN 38.3, UL1642, UL2054, IEC62133, FCC and CE approved. Certified compliant with EU Battery Directive 2006/66/EC.



Performance Specifications	General Parameters	Comments	
Nominal Voltage	12.8 volts		
Rated Capacity (77°F/25°C)	45 AH	Standard discharge 9A after	
Minimum Capacity (77°F/25°C)	42 AH	standard charge 9A	
Dimensions (in./mm)			
Length	7.70 / 195 (max)		
Width	5.20 / 130 (max)		
Height	7.20 / 183 (max)		
Life Expectation	Residual capacity is about 60% of rated capacity	CC charge at 9A to 14.6V then CV until current taper to 1A, rest 30 minutes, discharge at 9A to 10V. Temperature 60±9°F (20±5°C). Carry out 2500 cycles.	
Approximate Weight lbs./kg.	12.8/5.8		
Internal Resistance at 50% SOC	<35 mΩ	(77°F/25°C)	
Discharge Cut-Off Voltage	9.6V = 2.4 volts per cell	10.0V Recommended	
Charging Cut-Off Voltage	14.6V = 3.65 volts per cell		
Terminals	M6 button (female-threaded)		
Standard Charge	9A constant current (CC) charge to 14.6V, then constant voltage (CV) 14.6V charge until charge current declines to 1A		
Standard Discharge	Constant Current 9A, Cut-off Voltage 10.0V		
Cell Assembly	IFR 18650EC-1.5AH	4S30P	
Maximum Continuous Charge Current	20A @ 68°F (20°C)		
Maximum Continuous Discharge Current	20A @ 68°F (20°C)	Over current 40A (2S)	
Charge Temperature Range	32°F - 122°F (-0°C - 50°C)	60±25% Relative Humidity at Shipment Date	
Discharge Temperature Range	14°F - 122°F (-10°C - 50°C)		
Storage Temperature Range	40°F - 122°F (4°C - 50°C)	<3 months: 23°F-95°F (-5°C-35°C) >3 months-1 year: 32°F-77°F (0°C-25°C)	
Specific Energy	50.0 Wh/lb (99Wh/kg)		
Specific Density	124 Wh/L		
Protocol	SMBus	With RJ45	
Over Temperature Protection	60°±5°C Charge 65°±5°C Discharge		
Short Circuit Protection	2 <sup>nd</sup> level protection 30A fuse		
LED Indicator	Fuel Gauge	5 LED Indicator	

<b>Contact Information</b>			www.power-sonic.com	
DOMESTIC SALES Tel: +1-619-661-2020 Fax: +1-619-661-3650 national-sales@powersonic.com	CUSTOMER SERVICE Tel: +1-619-661-2030 Fax: +1-619-661-3648 customerservice@powersonic.com	TECHNICAL SUPPORT Tel: +1-619-661-2020 Fax: +1-619-661-3648 support@power-sonic.com	INTERNATIONAL SALES Tel: +1-650-364-5001 Fax: +1-650-366-3662 international-sales@power-sonic.com	
CORPORATE OFFICE • 7550 Panasonic Way • San Diego, CA 92154 • USA • Tel: +1-619-661-2020 • Fax: +1-619-661-3650				