Type CNP

UL Listed, CSA Certified Non conductive Conduit Liquid-Tight Flexible Non-Metallic Conduit (LFNC)



Construction

- Constructed of smooth inner thermoplastic PVC core with outer PVC cover bonded together with nylon reinforcing braid.
- Durable, sunlight resistant and flame retardant thermoplastic PVC that resists heat, oil and chemical breakdown.

Installation

- Conduit used with standard fittings for non-metallic conduit Type A for easy installation. IP 66/67 Rated when installed with approved fittings.
- Approved for both exposed and concealed locations. Rated for temperature ranges of -4°F to +140°F (-20°C to +60°C).
- Complies with UL Standard 1660 Type A conduit File No. E-75863; CSA C22.2 File No. LL15257; and NEC Article 356.
- Easy to install and cuts easily.
- Manufactured in a full range of trade sizes from 3/8" through 2".
- Flexible, but tough; crush, abrasion and strain resistant. Where abrasion, physical abuse or constant flexing are a factor.



Nylon Reinforced 3/8" through 2"

NEC Articles

- Article 250.102 Equipment Bonding Jumpers
- Article 250.134 (B) Equipment Grounding
- Article 300.22 (D) Information Technology Equipment
- Article 356 Liquid-Tight Flexible Nonmetallic Conduit (LFNC-A)
- Article 501.10 (B) (2) Class I Div. 2
- Article 502.10 (A) (2) and (B) (2) Class II Div. 1 & 2
- Article 503.10 (A) (3) and (B) Class III Div. 1 & 2
- Article 620.21 Elevator Wiring Methods
- Article 645.5 (E) (2) Under Raised Floors

www.ul.com www.nfpa.org www.nema.org www.csa-international.org www.naed.org

www.anametelectrical.com

See pages 30 for fittings







Type CNP

Orange or Gray thermoplastic PVC



Product Specifications

Ordering Information

1 reddet epeemedtiene								erdering intermation					
						Approx							
						Inside	Approx						
Elect	rical			Bend	Weight								
Trade	Size	Inside Diamete	r Ou	Outside Diameter		Radius	lbs.	Small Carton Standar			d Carton Reels		els
Inches	mm	Inches		Inches		Inches	PER	Length	NAED	Length	NAED	Length	NAED
		MIN. MAX	. N	ΛIN.	MAX.		100 FT.	Feet	PIN	Feet	PIN	Feet	PIN
3/8	12	. 485 – .505		. 755 – .775		2.5	15	100	38602	250	38601	800	38604
1/2	16	.620640		.910 – .930		3.0	21	100	38612	200	38611	500	38614
3/4	21	.815 – .835	1	1.150 - 1.170		4.0	30	100	38622	175	38621	400	38624
1	27	1.030 - 1.055		1.415 – 1.440		6.0	43			100	38631	300	38634
1-1/4	35	1.370 – 1.395 1.800			1.825	7.0	58			50	38641	200	38643
1-1/2	41	1.585 – 1.620 2.045 – 2.080			8.0	81			50	38651	100	38653	
2	53	2.045 - 2.080	2	2.605 -	2.640	9.0	122			50	38661	100	38663

Note: 1. Colors available on request.

2. Gray, change 3rd number in NAED code to "8"

TYPICAL SPECIFICATION:

Conduit shall be Anaconda SEALTITE® Type CNP. Conduit shall be constructed of smooth inner thermoplastic PVC core with outer oil-resistant and sunlight resistant PVC outer cover. Conduit shall have nylon reinforcing layer between the core and outer cover. Conduit shall be assembled with approved fittings to provide liquid-tight raceway for wiring. Conduit shall be UL listed and CSA certified as a Type "A" non-metallic conduit and be used in applications requiring a temperature range of -4 F to +140 F (-20 C to +60 C). Conduit IP 65/67 rated when installed with approved end fittinas.