



## Main

Range	Thalassa
Product name	Thalassa PLA
Device application	Multi-purpose
Product or component type	Suitable enclosure
Device short name	PLA
Enclosure nominal height	59.06 in (1500 mm)
Enclosure nominal width	29.53 in (750 mm)
Enclosure nominal depth	16.54 in (420 mm)
Enclosure mounting	Floor-standing
Device composition	1 door 1 rear panel 2 side part 1 top part 1 bottom part

## Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Plain front
Number of doors	1
Door opening side	Reversible 120 °
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Front Rear
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7032
Standards	IEC 62208 UL 508 A
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4/4X NEMA 3S NEMA 3X NEMA 5
Product certifications	UL/cUL listed Veritas DNV Marine

## Environment

IP degree of protection	IP65 completely sealed IEC 60529
IK degree of protection	IK10 plain door IEC 62262
fire resistance	1760 °F (960 °C) IEC 62208
ambient air temperature for storage	-31...194 °F (-35...90 °C)

## Offer Sustainability

Green Premium product	Green Premium product
-----------------------	-----------------------

Compliant - since 0940 - Schneider Electric declaration of conformity    Compliant - since 0940 - Schneider Electric declaration of conformity

Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------