

## End cover - D-PT 16 N - 3212060

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End cover, Length: 75.4 mm, Width: 2.2 mm, Height: 45.6 mm, Color: gray

The figure shows a version of the article

### Why buy this product

- End cover, enables the open terminal side to be covered

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 046356 494854
GTIN	4046356494854
Weight per Piece (excluding packing)	3.600 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### General

Color	gray
Material	PA
Flammability rating according to UL 94	V0

#### Dimensions

Width	2.2 mm
End cover width	2.2 mm

# End cover - D-PT 16 N - 3212060

## Technical data

### Dimensions

Length	75.4 mm
Height	45.6 mm
Height NS 35/7,5	52.6 mm

### General

Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27141111
eCl@ss 4.1	27141111
eCl@ss 5.0	27141133
eCl@ss 5.1	27141133
eCl@ss 6.0	27141133
eCl@ss 7.0	27141133
eCl@ss 8.0	27141133

## End cover - D-PT 16 N - 3212060

### Classifications

#### eCl@ss

eCl@ss 9.0	27141133
------------	----------

#### ETIM

ETIM 4.0	EC000886
ETIM 5.0	EC000886
ETIM 6.0	EC000886

#### UNSPSC

UNSPSC 6.01	30211827
UNSPSC 7.0901	39121424
UNSPSC 11	39121424
UNSPSC 12.01	39121424
UNSPSC 13.2	39121425