


# Short stroke cylinder AEVC-20-5-I-P

Part number: 188131

★ Core product range

FESTO



## Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	20 mm
Spring return force, retracted	5 N
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	single-acting pushing action
Design structure	Piston Piston rod
Position detection	No
Working pressure	1.5 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, advance stroke	180 N
Moving mass	14 g
Product weight	85 g
Mounting type	Optional with through hole with accessories
Pneumatic connection	M5
Materials note	Free of copper and PTFE
Material cover	Wrought Aluminum alloy Anodized
Material seals	NBR TPE-U(PU)
Material housing	Wrought Aluminum alloy Anodized
Material piston rod	High alloy steel