Test Jacks 4 mm System





Type BO 10

4mm panel mount test jack, nickel plated brass, M6 thread screw terminal. panel thickness 1.5-

8mm

Pin Diameter 4 mm

PART NO. / Housing color 930160000

BU 10 / BU 10 Au

4mm panel mount test jack, nickel/gold plated brass, M6 thread screw/ solder terminal. max. panel thickness 11mm

4 mm

930147000 (Nickel plated) 930147700 (Gold plated)

Technical Data

Contact Type jack Ø 4 mm

Connection Type M6 thread

Voltage Rating 30 VAC / 60 VDC

 Measurement Category (IEC61010)
 CAT I

 Current Rating*
 16 A

 Contact Resistance
 5 mOhm

 Mounting Type
 screw thread M6

Material Specifications

Jack Body nickel plated brass

Contact Spring –
Housing –

Environmental Conditions

Temperature Range $-25^{\circ}\text{C to } +70 \,^{\circ}\text{C (-13 to } 158^{\circ}\text{F)}$

Flamability Rating

Housing

jack Ø 4 mm

M6 thread, solder terminal 30 VAC / 60 VDC

CAT I 16 A 5 mOhm screw thread M6

nickel / gold plated brass


_


-25°C to +70 °C (-13 to 158°F)

-

Drawing

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.





^{*} Please consider derating graph on page 80.