



CONDUCTIVITY METER Model: 123-8777



FEATURES				
* Microcomputer circuit assures maximum	* Innovative feature with built-in automatic			
possible accuracy, provides special functions	temperature compensation values, adjustable			
and features.	between 0 to 5.0% per °C. Turning the dial to			
* Super large LCD display with contrast	0% per ℃ allows you to take uncompensated			
adjustment for best viewing angle.	conductivity readings.			
* Dual function meter's display.	* Wide automatic temperature compensation			
* Heavy duty & compact housing case, designed	range from 0 $^{\circ}$ to 60 $^{\circ}$, high accuracy.			
for easy carry out & operation.	* Carbon rod electrode for long life.			
* Records Maximum, Minimum and Average	* Show the conductivity & temperature values			
readings with RECALL.	at the same LCD display.			
* DATA HOLD function for stored the desired	* Temperature function for °C or °F be selected			
value on display.	by push button on front panel easily.			
* Auto shut off saves battery life.	* Built-in low battery indicator.			
* The portable conductivity meter provides fast,	* Wide applications: water conditioning, aquariums,			
accurate readings, with digital readability and	beverage, fish hatcheries, food processing,			
the convenience of a remote probe separately.	photography, laboratory, paper industry,			
* RS 232 PC serial interface.	quality control, school & college, water			
* Multi-measuring ranges: 200 uS, 2 mS, 20 mS.	conditioning.			

GENERAL SPECIFICATIONS				
Circuit	Custom one-chip of micro- processor LSI circuit.	Solution Temp. Coefficient	Preset to 2.0 % per ℃. Automatic from 0 to 60 ℃ (32-	
Display	* 13 mm(0.5") Super large LCD display with contrast adjustment for best viewing angle.	Factor	140 °F), with temperature compensation factor variable between 0 to 5.0% per °C.	
Measurement & ranges	* Dual function meter's display. 200 uS - 0.1 uS to 199.9 uS. 2 mS - 0.2 mS to 1.999 mS. 20 mS - 2 mS to 19.99 mS	Operating Temperature Operating Humidity	0 to 50 °C - main instrument. 0 to 60 °C - probe only. Max. 80% RH.	
Sensor	Temperature : °C, °F. Carbon rod electrode, high	Power Supply Power Current	006P DC 9V battery(heavy duty). Approx. DC 7.8 mA.	
Electrode	reliability.	Weight	350 g/0.77 LB	
Data Hold Memory Recall Power off	By push button Records Maximum, Minimum and Average readings with recall. Auto shut off saves battery life or manual off by push button.	Dimension	Main instrument: 180 x 72 x 32 mm (7.1 x 2.8 x1.3 inch). Conductivity probe: Round, 22 mm Dia. x 120 mm.	
Sampling Time Data Output Temperature	Approx. 0.8 second. RS 232 PC serial interface. Automatic adjusting	Accessories Included	Instruction manual	
Compensation Over input indication	0 ℃ to 60 ℃ (32 °F to 140 °F). Indication of "".	Optional Accessories	* RS232 cable, UPCB-01 * USB cable, USB-01 * Data Acquisition software, SW-U801-WIN * 1.413 mS calibration solution, CD-14.	