



Antennas



Wireless Application: Cellular, IoT, ISM, LMR, LPWAN, M2M

Antenna Connector Type: N-Type Female

Antenna Style: External

Antenna Type: Vehicular

Features

Product Type Features

Antenna Connector Type	N-Type Female
------------------------	---------------

Configuration Features

Band Type	3G, 4G, Cellular, GSM, LTE 2600, LTE 700, WiMAX 2300, WiMax 2500, WiMax 2600
Number of Ports	1
Antenna Style	External
Antenna Type	Vehicular

Signal Characteristics

Gain (Max)	3 dB
Frequency Band	698 – 960 MHz, 1710 – 2700 MHz

Operation/Application

Coverage Type	Omnidirectional
---------------	-----------------

Industry Standards

Wireless Application	Cellular, IoT, ISM, LMR, LPWAN, M2M
----------------------	-------------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # TRA6927M3PW-001
OMNI,DB,Ph,698/1710 MHz WHT,3 dBi,100W,

TE Part # TRA6927M3PB-003
OMNI,Ph,PMT,698/1710MHz BK,3dBi, 100W,NO

Customers Also Bought

TE Part #ETRAB4503
OMNI,PHE,NMO,450-470MHz, BLK, 3,150

TE Part #TRA6927M3NB-001
OMNI,Ph,NMO,698/1710 MHz BK,3 dBi,100W,

TE Part #ETRAB7603
OMNI,PhE,NMO,760-870MHz BK, 3,100,

TE Part #Y4506
YAGI,FWG,6,450-470MHz 10.2dBi,INT MT





TE Part #MAB8
Antenna Mounts: Thru-Hole

TE Part #FM2
MOUNT,HD,2.5 MAST



TE Part #LBM9034
MOUNT,MIR,3/4 STD,90DG/BRITE

TE Part #MB8-BP-25
MOUNT, MB8 25 BULK PACK

Documents

Product Drawings
OMNI,Ph,PMT,698/1710MHz BK,,100W,NGP
English

Datasheets & Catalog Pages
4G/3G Multiband No Ground Plane Phantom Antenna 698-960 MHz/1700-2700 MHz
English
4G/3G Multiband No Ground Plane Phantom Antenna 698-960 MHz/1700-2700 MHz
English