


Push-in/threaded L-fitting QSMLV-M5-3-I

Part number: 130830

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Mini |
| Nominal size | 1.7 mm |
| Type of seal on screw-in stud | Sealing ring |
| Assembly position | Any |
| Container size | 10 |
| Design structure | Push/pull principle |
| Operating pressure complete temperature range | -0.95 ... 6 bar |
| Temperature dependent working pressure | -0.95 ... 14 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -10 ... 80 °C |
| Maritime classification | see certificate |
| Nominal tightening torque | 1.33 Nm |
| Tolerance for nominal tightening torque | ± 20 % |
| Product weight | 5.1 g |
| Pneumatic connection, port 1 | Male thread M5 |
| Pneumatic connection, port 2 | for tubing, 3mm outside diameter |
| color of release ring | blue |
| Materials note | Conforms to RoHS |
| Material housing | PBT |
| Material release ring | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High alloy steel, non-corrosive |