

# Push-in fitting QSM-M7-6-I

Part number: 153321

★ Core product range

FESTO



## Data sheet

Feature	Value
Size	Mini
Nominal size	4.1 mm
Type of seal on screw-in stud	Sealing ring
Assembly position	Any
Container size	10
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 6 bar
Temperature dependent working pressure	-0.95 ... 14 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 80 °C
Maritime classification	see certificate
Nominal tightening torque	3.35 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	6.4 g
Pneumatic connection, port 1	Male thread M7
Pneumatic connection, port 2	For tubing outside diameter 6 mm
color of release ring	blue
Materials note	Conforms to RoHS
Material housing	Brass Nickel plated
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive