


Compact cylinder ADN-5/8"-1 1/2"-A-P-A

Part number: 557037

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 1.5 " |
| Piston diameter | 5/8" |
| Piston rod thread | UNF10-32 |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Conforms to standard | ISO 21287 |
| Piston-rod end | Male thread |
| Design structure | Piston Piston rod Profile barrel |
| Position detection | For proximity sensor |
| Variants | Single-ended piston rod |
| Working pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Ambient temperature | -4 ... 176 °F |
| Impact energy in end positions | 0.111 ft-lbf |
| Theoretical force at 6 bar, return stroke | 20.233 lbf |
| Theoretical force at 6 bar, advance stroke | 27.202 lbf |
| Moving mass with 0 mm stroke | 0.531 oz |
| Additional weight per 10 mm stroke | 0.283 oz |
| Basic weight for 0 mm stroke | 2.797 oz |
| Additional mass factor per 10 mm of stroke | 0.496 oz |
| Mounting type | Optional with through hole with internal (female) thread with accessories |
| Pneumatic connection | UNF10-32 |
| Material of flange screw | Steel |
| Material cover | Wrought Aluminum alloy Anodized |
| Material seals | NBR |
| Material of dynamic seals | TPE-U(PU) |
| Material piston rod | High alloy steel |
| Material cylinder barrel | Wrought Aluminum alloy Smooth anodized |