

## Universal Swivel Monitor Stand

MODEL NUMBER: **MR1815SWVL**



### Description

The MR1815SWVL Universal Swivel Monitor Stand not only frees up valuable space on your desk, table or workstation, it does so with chic, contemporary style that fits perfectly into any home or office décor. It rotates 360 degrees and features two extra-large wooden shelves measuring 18 x 15.25 inches. One shelf fits six inches above the other, allowing plenty of storage space between them for documents, paper clips, pens and other office necessities.

By holding your monitor six inches above the surface, the MR1815SWVL helps ease eye and neck strain. It supports up to 88 pounds, making it ideal for monitors and televisions up to 50 inches, as well as laptops, printers and fax machines. Sturdy metal legs with a rubber swivel wheel beneath secures the riser on smooth surfaces. The MR1815SWVL assembles in seconds using the included hardware.

### Features

Raises a Monitor 6 in. Above Your Desk's Surface

- Swivels 360°
- Frees up valuable work space
- Helps ease strain on eyes and neck
- For home or office
- Allows room for storage
- Ideal for monitors and televisions up to 50 in.

### Durable Construction

- Extra-large 18 x 15.25 in. wooden shelves support up to 88 lb.
- Sturdy metal legs with rubber swivel wheel secures riser on smooth surfaces
- Assembles easily in seconds using included hardware

### Highlights

- Extra-large 18 x 15.25 in. wooden shelves
- Sturdy metal legs with rubber swivel wheel
- Allows room underneath for keyboard storage
- Supports up to 88 lb.
- Assembles easily in seconds

### Package Includes

- Top shelf
- Bottom shelf
- (4) Metal legs
- (4) Finishing screws
- (4) Long screws
- Assembly instructions



- Contemporary easy-cleaning design fits any home or office décor

## Specifications

MODEL TEXT	
Key Benefit	Raises your monitor 6 in. above your desk, table or workspace's surface and swivels 360°. Ideal for monitors and televisions up to 50 in. and 88 lb.
PHYSICAL	
Mounting Location	Desktop
Unit Dimensions (hwd / in.)	6.9 x 18.1 x 15.3
Unit Dimensions (hwd / cm)	17.5 x 45.9 x 38.9
Unit Weight (lbs.)	10.1
Unit Weight (kg)	4.58
Material of Construction	wood and steel
Color	Black
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	40
FEATURES & SPECIFICATIONS	
Tools Necessary	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>