

PAFS21/BL/50M



STD WGT BLK NYL COND NC21 50M BLK



General Information

Extended Product Type	PAFS21/BL/50M
Product ID	7TCA296000R2207
EAN	5020963000096
Catalog Description	STD WGT BLK NYL COND NC21 50M BLK
Long Description	Standard Weight Conduit, Nominal Conduit Size 21mm, NW Conduit Size 17, Fine Conduit Pitch, Outside Diameter 21.2mm, Inside Diameter 16.5mm, Static Bend Radius 45mm, Reel Length 50 Meters, Polyamide (Nylon) 6, Black

Ordering

EAN	5020963000096
Minimum Order Quantity	1 piece
Customs Tariff Number	3926909996

Dimensions

Product Net Weight	2.998 kg
--------------------	----------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	508 mm
Package Level 1 Height	190.5 mm
Package Level 1 Depth / Length	508 mm
Package Level 2 Units	1 piece
Package Level 2 Width	508 mm
Package Level 2 Height	190.5 mm
Package Level 2 Depth / Length	508 mm

Additional Information

Brand / Label	Adaptaflex
Color	Black
Function	Indoors / Outdoors - Light Industrial, Buildings & Machinery
Material	Polyamide/Nylon 6
Product Main Type	ADAPTAFLEX FLEXIBLE CABLE PROTECTION

Product Name	"flexible conduit, nylon"
Product Type	Standard Weight Conduit with Fine Pitch
Special Functions	High Fatigue Life, Self Extinguishing, Halogen Free
UPC	786210147086

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	PAFS21/BL/50M
Instructions and Manuals	PAFS21/BL/50M

Classifications

ETIM 6	EC001175 - Corrugated plastic hose
UNSPSC	39131706

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

