

## Extension adapter - ENLAR-M-KV-M32/M40 - 1647682


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Step-up adapter, M32 to M40, including O-ring

RoHS

### Key Commercial Data

Packing unit	10 STK
GTIN	 4 017918 947095
GTIN	4017918947095

### Technical data

#### Dimensions

Length	23 mm
Length without connecting thread	16 mm
Connecting thread diameter	32 mm
Hexagon angular dimension	42 mm
Length of the connecting thread	7 mm

#### Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

#### General

Material	Brass, nickel-plated
Cable gland material	Nickel-plated brass
O-ring material	NBR
Outer thread	M32
Internal thread	M40
Color	silver

### Standards and Regulations

# Extension adapter - ENLAR-M-KV-M32/M40 - 1647682

## Technical data

### Standards and Regulations


Halogen-free	no
--------------	----

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>