



Suited for IP67 (wet) environments, the SGD provides a user-selectable 4-20mA or 0-10VDC absolute linear position signal over an 80-inch or 120-inch full stroke range option. Signal selection is simply made by connecting the appropriate pins on the included connector or selecting the proper wires in the optional cordset.

Additionally, this sensor is constructed with a rugged polycarbonate body, an extremely durable spring-loaded stainless steel measuring cable and a mounting bracket that lets the customer mount this sensor in just about any direction. The SGD is in stock for quick delivery.

Customized options are also available for OEM customers.

# SGD

# Cable Actuated Sensor 4..20mA • 0..10 Vdc Output Signal

**Compact Mid-Range String Pot • Absolute Position** 

80, 120-inch Stroke Range Options

Polycarbonate Enclosure • IP67

In Stock for Quick Delivery

#### **Specifications**

Stroke Range 80 inches (2032 mm), 120 inches (3048 mm)

**User Selectable Output** 4...20 mA (2-wire) / 0...10 Vdc

Signal

Input Voltage, 4...20 mA 8-40 VDC option

Input Voltage, 0...10 Vdc 12-32 VDC

option

Accuracy .35% FS. Repeatability .05% FS.

Resolution essentially infinite

Measuring Cable .019-inch dia. nylon-coated stainless steel

**Maximum Acceleration** 10 g

Measuring Cable Tension 9 oz. (2,5 N) ±30%

Sensor plastic-hybrid precision potentiometer

Cycle Life

**Electrical Connection** M12 connector (mating plug included)

Enclosure glass-filled polycarbonate

**Environmental** 

**Operating Temperature** 0° to 160° F (-18° to 70° C)

Weight, 80-inch (not

.6 lbs. (272 g)


including bracket)

Weight, 120-inch (not 1 lb. (453 g)

including bracket)


#### **Output Signal**

pring loaded cable reel




signal endpoint tolerances Output Sianal\* 0% fs. 100% fs. 4..20 mA 4-4.25 mA 19.2-20 mA 0..10 Vdc 0 - .2 Vdc 9.5 - 10 Vdc


\*note: signal endpoints are set at the time of manufacture and cannot be adjusted




# field installable connector (included) contact view 2.4" [60mm] — customer supplied electrical cable, (.25 in [6 mm] max. dia.)


#### cordset, part no. 9036810-0040 (optional)










# Mounting Options (SGD-80-3):






# Mounting Options (SGD-120-3):









SENSOR SOLUTIONS /// SGD 12//2015 Page 2

## SGD-80-3 w/ Mounting Bracket



## SGD-120-3 w/ Mounting Bracket



SENSOR SOLUTIONS /// SGD 12//2015 Page 3

#### **Ordering Information**



Part No.

SGD-80-3

80-inch stroke range, 4-20 mA / 0-10 Vdc output M12 connector, IP67 environments, mounting bracket included Part No.

SGD-120-3

120-inch stroke range, 4–20 mA / 0–10 Vdc output M12 connector, IP67 environments, mounting bracket included



# Optional Cordset

Part No.

9036810-0040

for short-run connections, a convenient optional 13-ft. cordset with a 4-pin M12 connector is available for the SGD-80-3 and SGD-120-3.

#### **NORTH AMERICA**

Measurement Specialties, Inc., a TE Connectivity company 20630 Plummer Street Chatsworth, CA 91311 Tel +1 800 423 5483 Tel +1 818 701 2750

Fax +1 818 701 2799 info@celesco.com

#### TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

SGD 12/01/2015

SENSOR SOLUTIONS /// SGD 12//2015 Page 4