


Interface CAMC-F-EP

Part number: 1911917
 ☆ Core product range



Data sheet

Feature	Value
Dimensions W x L x H	19 mm x 90 mm x 65 mm
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Storage temperature	-25 ... 70 °C
Relative air humidity	5 - 95 % non-condensing
Protection class	IP20 in assembled condition
Ambient temperature	0 ... 50 °C
Product weight	75 g
Mounting type	Plug-in module for CMMP-AS...-M3
Materials note	Contains PWIS substances Conforms to RoHS
Assembly position	Any
Protocol	EtherNet/IP
Communications profile	FHPP
Baud rate	10/100 Mbit/s (Full/Half)
Topologies	Star Ring Line
Media redundancy	DLR
IP address allocation	FCT DHCP BOOTP DIP switches
Fieldbus interface	2x socket RJ45
Minimum cycle time	1 ms
LED displays	- Ethernet communication activity - Ethernet line monitoring - Module status - Networkstatus
Configuration support	EDS
Parameters configuring	- FCT
Additional functions	AddressConflictDetection (ACD) Integrated Switch