



# Toothed belt axis EGC-80-1000-TB-KF-0H-GK

Part number: 3013357

☆ Core product range

FESTO



## Data sheet

Feature	Value
Effective diameter of drive pinion	28.65 mm
Working stroke	1,000 mm
Size	80
Stroke reserve	0 mm
Toothed-belt stretch	0.24 %
Toothed-belt pitch	3 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electromechanical linear axis With toothed belt
Motor type	Stepper motor Servomotor
Max. acceleration	50 m/s <sup>2</sup>
Max. speed	5 m/s
Repetition accuracy	±0,08 mm
Duty cycle	100%
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Area moment of inertia 2nd degree I <sub>x</sub>	844E+03 mm <sup>4</sup>
Area moment of inertia 2nd degree I <sub>y</sub>	1,160E+03 mm <sup>4</sup>
Max. force F <sub>y</sub>	3,050 N
Max. force F <sub>z</sub>	3,050 N
Max. idling displacement resistance	28 N
Max. torque M <sub>x</sub>	36 Nm
Max. feed force F <sub>x</sub>	350 N
Torsional mass moment of inertia I <sub>t</sub>	551E+03 mm <sup>4</sup>
Mass moment of inertia J <sub>H</sub> per meter of stroke	0.19 kgcm <sup>2</sup>
Mass moment of inertia J <sub>L</sub> per kg of working load	2.05 kgcm <sup>2</sup>
Feed constant	90 mm/U
Material of end caps	Wrought Aluminum alloy Anodized
Material of profile	Wrought Aluminum alloy Anodized
Materials note	Contains PWIS substances Conforms to RoHS
Material drive cover	Wrought Aluminum alloy Anodized
Material guide slide	Steel
Material guide rail	Steel
Material pulleys	High alloy steel, non-corrosive
Material slide	Wrought Aluminum alloy Anodized
Material toothed belt clamping piece	Stainless steel casting
Material toothed belt	polychloroprene with glass cord and nylon coating