

# Rittal – The System.

Faster – better – everywhere.

## Cable gland HD – HD 2410.020

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Cable gland HD – HD 2410.020

created: 19.03.2018 build on [www.rittal.com/us-en](http://www.rittal.com/us-en)



## Product description

**Version:** Standard

**Benefits:** Smooth, solid exterior surfaces effectively prevent the accumulation of harmful micro-organisms.  
Much easier, and therefore cheaper to clean compared with conventional cable glands.

**Applications:** Production and packaging of food and beverages  
Clean room technology (e.g. pharmaceuticals)  
Biotechnology  
Chemical industry

**Material:** Cap nut: Stainless steel 1.4305 (AISI 303)  
Seal: Conforms to FDA 21 CFR 177.2600

**Protection category IP to IEC 60 529:** IP 68 (5 bar, 30 min.)

**Protection category IP to DIN 40 050-9:** IP 69K

## Product features

**Ambient temperature range:** -20°C...+100°C

**Thread:** M20 x 1.5

**Operating temperature (max.):** 100 °C (212 °F)

**Cable entry:** For cable diameter: 6 mm - 12 mm

<b>Packaging unit:</b>	5 pc(s).
<b>Weight/packaging unit:</b>	0.35 kg (0.8 lb.)
<b>EAN:</b>	4028177162204
<b>Customs tariff number:</b>	73181900
<b>ETIM 6.0:</b>	EC000441
<b>ETIM 5.0:</b>	EC000441
<b>eCl@ss 8.0/8.1:</b>	27149109
<b>eCl@ss 7.0/7.1:</b>	27189265
<b>eCl@ss 6.0/6.1:</b>	27189265
<b>eCl@ss 5.1/5.1.4:</b>	27180102
<b>Product description (long):</b>	HD Cable gland, stainless steel 1.4305, size: M20x1,5, for cables Ø 6-12 mm, Standard version

## Approvals

<b>Certificates:</b>	DGUV EAC
<b>Declarations:</b>	Manufacturer's declaration